


KPS SMD Comm X7R, Ceramic, 47 uF, 20%, 25 VDC, X7R, 2220-2

**Dimensions**

L	6mm +/-0.5mm
W	5mm +/-0.5mm
T	5mm +/-0.50mm
B	1.6mm +/-0.3mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	200

General Information

Supplier:	KEMET
Series:	KPS SMD Comm X7R
Style:	Stacked Chip
Description:	SMD, MLCC, Stacked, Double Chip, Temperature Stable
Features:	Temperature Stable
RoHS:	Yes
Termination:	Tin
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours
Chip Size:	2220-2

Specifications

Capacitance:	47 uF
Capacitance Tolerance:	20%
Voltage DC:	25 VDC
Dielectric Withstanding Voltage:	62.5 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	3.50% 120Hz 25C
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	11 MOhms