

Product data sheet

Specifications



Repacked, contactor, Acti9 iCT+, 20A, 1P UC, 230VAC

A9C15030W



This repacked option saves 0.789 over the standard condition

Main

range of product	Acti9
Product name	Acti9 iCT+
Product or component type	Contactors
Device short name	iCT+
Device application	Control circuit
Poles	1P
[Ie] rated operational current	20 A AC-7A 20 A AC-7B
Pole contact composition	1 NO
Network type	AC
Control type	Remote control
[Uc] control circuit voltage	230 V AC 50 Hz

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	250 V AC 50 Hz
Maximum power	3.6 kW at 250 V AC
[Ui] rated insulation voltage	300 V
Control signal type	Maintained
Switching frequency	6 switching operation/minute
Local signalling	Color indicator
Hold-in power consumption in VA	1.1 VA
inrush power in VA	11 VA
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	60 mm
Product weight	70 g
Colour	White
Mechanical durability	5000000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical durability	5000000 cycles
Connections - terminals	Tunnel type terminal2 cable(s) 1.5 mm² rigid Tunnel type terminal2 cable(s) 1.5 mm² flexible with ferrule Tunnel type terminal2 cable(s) 2.5 mm² rigid Tunnel type terminal2 cable(s) 2.5 mm² flexible Tunnel type terminal1 cable(s) 4 mm² rigid Tunnel type terminal1 cable(s) 4 mm² flexible
Tightening torque	1 N.m
Wire stripping length	10 mm
Product compatibility	No auxiliary
Compatibility code	ICT+
Market segment	Residential Small commercial

Environment

Standards	EN 60669-2-1
Product certifications	NF
Noise level	10 dB
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-40...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.700 cm
Package 1 Width	6.700 cm
Package 1 Length	8.200 cm
Package 1 Weight	86.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.908 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.8 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

429095ee-388a-4184-bea4-16f87e374975

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins