



Figure similar

SCALANCE X308-2LH+ managed plus IE switch, 2x 1000 Mbit/s SM SC, 1x 10/100/1000 Mbit/s, 7x 10/100 Mbit/s RJ45 ports, LED diagnostics, error signaling contact with select/set pushbutton, PROFINET IO device, network management, integrated redundancy manager, office features (RSTP, VLAN, IGMP,..) C-PLUG in scope of supply.

<b>product type designation</b>	<b>SCALANCE X308-2LH+</b>
<b>transfer rate</b>	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
<b>interfaces / for communication / maximum configuration for modular devices</b>	
number of electrical ports / maximum	8
number of optical ports / maximum	2
<b>interfaces / for communication / integrated</b>	
number of electrical connections	8
• for network components or terminal equipment	
number of 10/100 Mbit/s RJ45 ports / integrated	7
• with securing collar	
number of 10/100/1000 Mbit/s RJ45 ports / integrated	1
• with securing collar	
number of 1000 Mbit/s SC ports	2
• for single mode (LH+)	
<b>interfaces / other</b>	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
<b>signal inputs/outputs</b>	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
<b>supply voltage, current consumption, power loss</b>	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	No
<b>type of voltage / 1 / of the supply voltage</b>	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	9.6 W
• supply voltage / 1 / rated value	18 ... 32 V
• consumed current / 1 / maximum	0.4 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes

• fuse protection type / 1 / at input for supply voltage	F 3 A / 32 V
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP30
<b>design, dimensions and weights</b>	
design	compact
width	120 mm
height	125 mm
depth	123 mm
net weight	1.4 kg
fastening method	When used in shipbuilding, installation on a 35 mm standard mounting rail is not permitted.
• 19-inch installation	No
• 35 mm top hat DIN rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of <math>\leq 0.3 \text{ s}</math>	100
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
product function / switch-managed	Yes
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	Yes
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
<b>product functions / diagnostics</b>	
product function	
• port diagnostics	Yes

<ul style="list-style-type: none"> <li>● statistics Packet Size</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● statistics packet type</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● error statistics</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● SysLog</li> </ul>	Yes
<b>product functions / VLAN</b>	
product function	
<ul style="list-style-type: none"> <li>● VLAN - port based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● VLAN - protocol-based</li> </ul>	No
<ul style="list-style-type: none"> <li>● VLAN - IP-based</li> </ul>	No
<ul style="list-style-type: none"> <li>● VLAN dynamic</li> </ul>	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
protocol / is supported / GVRP	Yes
<b>product functions / DHCP</b>	
product function	
<ul style="list-style-type: none"> <li>● DHCP client</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● DHCP Option 82</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● DHCP Option 66</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● DHCP Option 67</li> </ul>	Yes
<b>product functions / redundancy</b>	
product function	
<ul style="list-style-type: none"> <li>● ring redundancy</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● High Speed Redundancy Protocol (HRP)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● high speed redundancy protocol (HRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> <li>● media redundancy protocol (MRP) with redundancy manager</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● redundancy procedure STP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● redundancy procedure RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● redundancy procedure MSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● passive listening</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>● STP/RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● STP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● RSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● MSTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● RSTP big network support</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● LACP</li> </ul>	Yes
<b>product functions / security</b>	
product function	
<ul style="list-style-type: none"> <li>● ACL - MAC-based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● ACL - port/MAC-based</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● IEEE 802.1x (radius)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● broadcast/multicast/unicast limiter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● broadcast blocking</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>● SSH</li> </ul>	Yes
<b>product functions / time</b>	
product function	
<ul style="list-style-type: none"> <li>● SICLOCK support</li> </ul>	Yes
protocol / is supported	
<ul style="list-style-type: none"> <li>● NTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● SNTP</li> </ul>	Yes
<ul style="list-style-type: none"> <li>● IEEE 1588 profile default</li> </ul>	No
<b>standards, specifications, approvals</b>	
standard	
<ul style="list-style-type: none"> <li>● for FM</li> </ul>	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4

<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	UL 60950-1, CSA C22.2 No. 60950-1 EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005	
MTBF	25 a	
reference code		
<ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> <li>• according to IEC 81346-2:2019</li> </ul>	KF KFE	
<b>standards, specifications, approvals / CE</b>		
certificate of suitability / CE marking	Yes	
<b>standards, specifications, approvals / hazardous environments</b>		
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X	
<ul style="list-style-type: none"> <li>• from CSA and UL</li> </ul>	UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4	
certificate of suitability		
<ul style="list-style-type: none"> <li>• CCC / for hazardous zone according to GB standard</li> <li>• CCC / for hazardous zone according to GB standard / as marking</li> </ul>	Yes; GB3836.1, GB3836.8 Ex nA IIC T4 Gc	
<b>standards, specifications, approvals / other</b>		
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007	
<ul style="list-style-type: none"> <li>• C-Tick</li> <li>• KC approval</li> <li>• railway application in accordance with EN 50155</li> </ul>	Yes Yes No	
<b>standards, specifications, approvals / marine classification</b>		
Marine classification association		
<ul style="list-style-type: none"> <li>• French marine classification society (BV)</li> <li>• Det Norske Veritas (DNV)</li> <li>• DNV GL</li> <li>• Korean Register of Shipping (KRS)</li> <li>• Polski Rejestr Statkow (PRS)</li> </ul>	Yes No Yes Yes Yes	
<b>further information / internet links</b>		
internet link		
<ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Selection guide for cables and connectors</li> <li>• to website: Image database</li> <li>• to website: CAx-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a> <a href="https://sie.ag/2QdlxcP">https://sie.ag/2QdlxcP</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>	
<b>security information</b>		
security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial security measures that may be implemented, please visit <a href="https://www.siemens.com/industrialsecurity">https://www.siemens.com/industrialsecurity</a>. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under <a href="https://www.siemens.com/cert">https://www.siemens.com/cert</a>. (V4.6)</p>	
<b>Approvals / Certificates</b>		
<b>General Product Approval</b>	<b>EMC</b>	<b>For use in hazardous locations</b>

[Manufacturer Declaration](#)

[Miscellaneous](#)



[ATEX-Zone 2-Declaration](#)



[FM](#)

For use in hazardous locations | Declaration of Conformity | Test Certificates

[CCC-Ex](#)



[Manufacturer Declaration](#)



[Type Test Certificates/Test Report](#)

Marine / Shipping



[NK / Nippon Kaiji Kyokai](#)



Marine / Shipping | Environment



last modified:

11/9/2023