

Detached triple servo drive 6A continous current for cold plate, 24A peak, IP65

ILM62DDD24D1000

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	PacDrive 3	
Product or Component Type	Detached servo drive	
Device short name	ILD	

Complementary

Product compatibility	Servo motor MH3 Motor asynchronous motor Servo motor SH3 6 A Servo motor SH3 4.4 A	
[Us] rated supply voltage	250700 V	
Line Rated Current	6 A active cold plate 4.4 A passive cold plate	
Safety Function	STO (safe torque off)	
type of cooling	Fanless Water Cooled Passive cold plate	
Number of mounting holes	4	
Net Weight	11.7 lb(US) (5.3 kg)	

Environment

IP Degree of Protection	IP65	
Standards	EN/IEC 61800-5-1 EN/IEC 61800-3 EN/IEC 62061 UL 618000-5-1 EN/IEC 61800-5-2 CSA C22.2 No 274 EN/ISO 13849-1	
Directives	2014/30/EU - electromagnetic compatibility 2006/42/EC - machinery 2014/35/EU - low voltage directive	
Product Certifications	CE cURus	

Ordering and shipping details

Category	US1PC5218351
Discount Schedule	PC52
GTIN	3606485468846
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.77 in (17.2 cm)
Package 1 Width	12.80 in (32.5 cm)
Package 1 Length	16.73 in (42.5 cm)
Package 1 Weight	14.3 lb(US) (6.5 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

○ Repack and remanufacture		
Take-back	No	