

Vacuum generator OVPN-20-L2-PG14-G34-UA

Part number: 8199144

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Nominal size, Laval nozzle	2 mm
Grid dimension	29.4 mm
Silencer design	Open
Mounting position	Any
Ejector characteristic	High suction rate
Integrated function	Open silencer
Design	Vacuum generator 2-stage
Symbol	00991489
Operating pressure for max. suction flow rate	0.5 MPa
Operating pressure for max. suction flow rate	5 bar
Operating pressure for max. suction flow rate	72.5 psi
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Operating pressure	14.5 psi ... 116 psi
Operating pressure for max. vacuum	0.79 MPa
Operating pressure for max. vacuum	7.9 bar
Operating pressure for max. vacuum	114.55 psi
Max. vacuum	81 %
Nominal operating pressure	0.6 MPa
Nominal operating pressure	6 bar
Nominal operating pressure	87 psi
Max. suction flow rate against atmosphere	317 l/min
Air supply time at nominal operating pressure	0.19 s
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Media temperature	0 °C ... 60 °C
Recommended cleaning/purification	Soapsuds (except silencers)
Sound pressure level at nominal operating pressure	66 dB(A)
Ambient temperature	0 °C ... 60 °C
Product weight	470 g
Type of mounting	With mounting bracket
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	Open silencer

Feature	Value
Vacuum connection	G3/4
Material connecting thread	POM
Material seals	NBR
Material receiver nozzle	Reinforced PA
Material housing	POM
Material silencer	Reinforced PA Polyurethane foam
Material screws	High-alloy stainless steel
Material transmitter nozzle	Reinforced PA