

7502PF

Biodegradable, chemical resistant and powder-free disposable glove with no accelerator





Bio-degradable and powder-free glove made without accelerators found in regular nitrile gloves. This reduces the chances of skin irritation in those with allergies or sensitive skin.

Features

- ▲ 100% nitrile disposable glove with textured fingertips
- ▲ Engineered with Eco Best Technology, making the glove biodegradable in biologically active landfills
- ▲ Non-sterile, silicone and latex free
- ▲ Accelerator-free formulation protects very sensitive skin
- ▲ Protects from a wide array of chemical hazards while avoiding type and type IV latex allergies
- ▲ Low-modulus formulation to improve fit and reduce fatigue
- ▲ Ambidextrous aiding the ability to easily put on and remove
- ▲ AQL 1.5



Certifications

<p>CAT III</p>  <p>2777</p>	<p>FOOD SAFE</p> 	<p>EN 374-1: 2016/ Type C</p>  <p>K, T</p>	<p>EN 374-5: 2016</p>  <p>Micro Organisms + Virus</p>
---	--	---	--

Suitable industries & applications

Industries

- ▲ Food Production
- ▲ Automotive
- ▲ Healthcare
- ▲ Education and Research

- ▲ Manufacturing
- ▲ Chemicals
- ▲ Highways and Infrastructure

Applications

- ▲ Component and Product Assembly
- ▲ Vehicle Repairs and Maintenance

- ▲ Chemical Handling and Containment
- ▲ Food Preparation and Handling
- ▲ Laboratory Analysis

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

7502PF

Biodegradable, chemical resistant and powder-free disposable glove with no accelerator

Product information

Materials	Liner:	Unlined/Unsupported
	Coating:	Nitrile
Colour	Blue	
Cuff Style	Beaded	

Ordering information

6/XS	SHO75020	Items per Case 10 x Box of 200 *
7/S	SHO75021	
8/M	SHO75022	
9/L	SHO75023	
10/XL	SHO75024	
11/XXL	SHO75025	

* NB. XXL = Box of 180

Additional information

<p>Certification legend</p>  <p>or click here</p>	<p>Declaration of conformity</p>  <p>or click here</p>	<p>View product online</p>  <p>or click here</p>
---	--	--

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747