




EMI & EMC Solutions > EMI Shielding > Board Level Shielding (BLS)



Shielding Type: **One-Piece**

Frame Material: **Aluminum**

Features

Product Type Features

Shielding Type	One-Piece
Frame Material	Aluminum

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability













Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 2108964-1 Stamped Antenna, SMD, Wi-Fi, 2.4 + 5GHz</p>	 <p>TE Part # 2108823-1 Stamped antenna, SMD, 617-7125 MHz</p>	 <p>TE Part # 2108840-1 Ceramic patch ant, L1+G1 &amp; L2+E5b</p>	 <p>TE Part # 2195771-1 LTE/ 5G DAS Antenna</p>
 <p>TE Part # 2108847-1 Ceramic patch antenna, L1+G1 &amp; L2</p>	 <p>TE Part # 2108517-2 DUAL BAND WiFi ANTENNA, STAMPED METAL, SMD</p>	 <p>TE Part # 1513504-1 100930LF MOLDED STAMPED ANTENNA</p>	 <p>TE Part # 1513634-1 400411LF Molded Stamped Antenna</p>
 <p>TE Part # 2118316-1 Single Band WiFi, 5Ghz, Stamped, PCB Mt.</p>	 <p>TE Part # 1513164-1 MOLDED STAMPED ANTENNA</p>	 <p>TE Part # 2108844-1 Ceramic ant, L1+G1 &amp; L2+L5</p>	 <p>TE Part # 2108848-1 Ceramic patch antenna, L1+G1 &amp; L2</p>

Customers Also Bought

 <p>TE Part #5177983-6 0.8FH,R05H.5,140,08/Sn,TU</p>	 <p>TE Part #9-2176388-8 RQ 1206 102R 0.1% 10PPM 5K RL</p>	 <p>TE Part #8-1415537-0 SR6B6K24</p>	 <p>TE Part #2-1617758-7 FCB-205-0119M=M83536/1-019M</p>
---	--	--	---





TE Part #8-1393640-3  
V42254B2201C410=PC612 FEDERLEI



TE Part #5-102617-4  
12 MODII HDR DRRA SHRD LF



TE Part #173924-1  
2 P ACTION PIN UMNL



TE Part #173926-1  
4 P ACTION PIN UMNL



TE Part #2394113-3  
H&S 70mm, Cable cover



TE Part #969973-4  
2x4P HV100 REC. CON, SMD, GOLD, BLISTER

Documents

Product Drawings

1 PC STD SHIELD, AL-26.21X26.21X5.08MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2118708-4\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2118708-4\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2118708-4\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Board Level Shield (BLS) Quick Reference Guide

English

Product Specifications

Application Specification

English