

M18 FPD3-O

M18 FUEL™ PERCUSSION DRILL

- Higher power efficiency under load with outstanding torque of 158 Nm
- Extremely compact design of 175 mm length for access into tight spaces
- AUTOSTOP™ control mode offers enhanced safety for the operator by preventing over-rotation in a bind-up
- 13 mm metal chuck for quick bit changes and bit retention
- Fastest drilling and driving applications under load
- Brighter LED workspace illumination
- Fuel gauge displays remaining charge
- All metal reversible belt clip to hang your tool quickly and easily
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	0 - 500/ 0 - 2,100
Max. drilling wood/ steel/ masonry (mm)	89/ 16/ 16
Max. percussion rate (bpm)	0 - 33,000
Max. torque (Nm)	158
Weight with battery pack (EPTA) (kg)	2.2 (M18 B5)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933498060