



Datasheet

ENGLISH

Stock No: 575-138

RS Pro A11 Abrasive Mounted Point, 19860rpm, 6mm Shaft Diameter



Mounted Abrasive Points

Pink abrasive mounted points supplied in bags of 10.

Product Details

Pink Abrasive Points

Applications include deburring, smoothing, cleaning, polishing and general finishing operations

Maximum operating speeds depend on shape and size of wheel, size of shank and amount of overhang

Operating speeds quoted are for an overhang of 13mm. If an overhang of more than 13mm is used then the maximum operating speeds are reduced. See the Health and Safety Executive Publication Ref HS(G)17 and the European Safety Co issued by the Federation of European Producers of Abrasive Products (FEPA No 12GB74)



ENGLISH

Caution

When using Mounted Points always observe the safety instructions: do not exceed the maximum operating speeds and overhang of points; always wear eye protection; check that the bearings and collet of the grinder are not worn; avoid excessive pressure which could damage the mandrel.

Specifications:

Maximum Safe Speed	15000rpm
Maximum Speed at 13 mm Overhang	19860rpm
Shape Reference	A11
Shaft Diameter	6mm
Number in Pack	10