

Technical data


4T-33013

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage



VISUAL (S)



4T-33013

Single row tapered roller bearings

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	65 mm
D - External diameter	100 mm
B - Bearing/Inner ring width	27 mm
C - Outer ring width	21 mm
T - Total width	27 mm
d1 - External diameter inner ring	83 mm
a - Charge load application point	21,5 mm
rs - Min fillet radius	1,5 mm
r1s - Min fillet radius	1,5 mm
Mass	0,742 kg
ISO 355 reference	T2CE065

PRODUCT PERFORMANCE

C - Dynamic load	108000000 mN
C0 - Static load	156000000 mN
Cu - Fatigue limit load	19000000 mN
A2 - Rating life coefficient	1
e - Coefficient	0.35
Y0 - Static axial load coefficient	0.95
Y2 - Upper axial load coefficient	1.72
N lim - Oil lubrication limit speed	27600 °/s
N lim - Grease lubrication limit speed	20400 °/s
Tmin - Min operating temperature	233,15 °K



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

4T-33013

Single row tapered roller bearings

PRODUCT PERFORMANCE

Tmax - Max operating temperature	393,15 °K
---	-----------

ABUTMENT

da max - Max shoulder diameter IR	72 mm
--	-------

db min - Min IR shoulder diameter	73,5 mm
--	---------

Da min - Min shoulder diameter OR	89 mm
--	-------

Da max - Max shoulder diameter OR	91,5 mm
--	---------

Db min - Min OR shoulder diameter	96 mm
--	-------

Ca - Min clearance	5 mm
---------------------------	------

Cb - Min clearance	6 mm
---------------------------	------

ra max - Max fillet radius	1,5 mm
-----------------------------------	--------

r1a - Max fillet radius	1,5 mm
--------------------------------	--------



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

