





FAG

61812-2RZ-Y

Deep groove ball bearing

Deep groove ball bearing 618...-2RZ-Y, single row, shields, brass sheet metal cage

Technical information



Your current product variant

Sealing	2RZ	Non-contact seal on both sides
Cage	Y	Brass sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	L565	Grease (L565/customer specific)
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	60 mm	Bore diameter
D	78 mm	Outside diameter
B	10 mm	Width
C _r	12,600 N	Basic dynamic load rating, radial
C _{0r}	11,100 N	Basic static load rating, radial
C _{ur}	710 N	Fatigue load limit, radial
n _G	10,400 1/min	Limiting speed
n _{gr}	6,300 1/min	Reference speed
≈m	0.105 kg	Weight



Mounting dimensions

$d_{a\min}$	62 mm	Minimum diameter shaft shoulder
$D_{a\max}$	76 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0.3 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0.3 mm	Minimum chamfer dimension
D_1	72.55 mm	Shoulder diameter outer ring
D_2	74.5 mm	Caliber diameter outer ring
d_1	65.6 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Calculation factors

f_0	16.3	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides