




Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **82 Newton**
Product Length: **134 mm [5.27 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	82 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	32 mm[1.26 in]
Product Length	134 mm[5.27 in]
Product Width	2.6 mm[.102 in]
Product Thickness	1 mm[.039 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>





Compatible Parts

 TE Part # 8296514002 CM-SCE-SHT-2.5-9	 TE Part # EC6474-000 13611420	 TE Part # EC6495-000 13611441	 TE Part # 227424-000 CM-SCE-TP-2.5K-1/2-6H-9
 TE Part # EC6540-000 13611921	 TE Part # EC6545-000 13611926	 TE Part # EC6547-000 13611928	 TE Part # EC6551-000 13611932



 TE Part # EC6460-000 13611406	 TE Part # EC6525-000 13611906	 TE Part # EC6469-000 13611415	 TE Part # EC6480-000 13611426
 TE Part # EC6500-000 13611447	 TE Part # EC6505-000 13611606	 TE Part # EC6530-000 13611911	 TE Part # EC6491-000 13611437
 TE Part # EC6513-000 13611707	 TE Part # EC6531-000 13611912	 TE Part # EC6532-000 13611913	 TE Part # EC6453-000 13611303

Customers Also Bought

 TE Part #350735-4 12P UMNL PLUG HSG UL94VO	 TE Part #1-284506-2 12 POS TERMI-BLOK PLUG STAC 3,	 TE Part #124045-E SMCB 50 F AB VV 6-03 CLHD * H007 137 E00	 TE Part #1-770966-0 02P MINI UMNL R/A HDR ASSY SN
 TE Part #5177983-3 0.8FH,R05H.5,080,08/Sn,TU	 TE Part #5161390-4 04P.DIP SWITCH ASSY	 TE Part #CAT-M5833-F3492A Female-on-Board Connector, Top Entry	 TE Part #5-2176330-4 CRGP 2010 270K 1%

Documents

4-160968-2

Standard Cable Tie, Bag, 18.5 lbf Tensile Strength, 82 Newton Tensile Strength, 134 mm [5.27 in] Length, 2.6 mm [.102 in] Width, Black



Product Drawings

CABLE TY 134X2.6 BLACK

English

Datasheets & Catalog Pages

CABLE TIES

English