

36502C8R2JTDG

✓ ACTIVE

Sigma | Sigma 3650

TE Internal #: 4-1879023-7

High Frequency Inductor, 1008, 8.2 μ H, 170 mA, 6 ohm DC

Resistance, 5 %, Surface Mount, Taped & Reeled, 2.92 mm [.114 in]

Length, Sigma 3650

[View on TE.com >](#)



Passive Components > Inductors > High Frequency & RF Inductors



Inductor Type: **High Frequency**

Package Size Code: **1008**

Inductance: **8.2 μ H**

Current Rating (Max): **170 mA**

DC Resistance: **6 Ω**

Features

Product Type Features

Inductor Type	High Frequency
Package Size Code	1008
Element Type	Wire Wound

Electrical Characteristics

Self Resonant Frequency	.025 GHz
Inductance	8.2 μ H
Current Rating (Max)	170 mA
DC Resistance	6 Ω
Passive Component Tolerance	5 %

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Dimensions

Product Length	2.92 mm[.114 in]
Product Width	2.79 mm[.109 in]
Product Height	2.13 mm[.083 in]

Usage Conditions

Operating Temperature Range	-40 – 125 $^{\circ}$ C
-----------------------------	------------------------

Packaging Features



Packaging Method	Taped & Reeled
------------------	----------------

Other

Inductor Quality Factor	15
-------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1624112-8
3650 0603 68nH 5% 2K RL



TE Part # 6-1624113-2
3650 0805 0.56uH 5% 2K RL



TE Part # 4-1879023-8
3650 1008 10uH 5% 2K RL



TE Part # 5-1624113-2
3650 0805 0.22uH 5% 2K RL



Also in the Series | [Sigma 3650](#)



Customers Also Bought



Documents

[Product Drawings](#)
[3650 1008 8.2uH 5% 2K RL](#)
English

[CAD Files](#)
[3D PDF](#)

3D

Customer View Model
[ENG_CVM_CVM_4-1879023-7_BA.2d_dxf.zip](#)
English

Customer View Model
[ENG_CVM_CVM_4-1879023-7_BA.3d_igs.zip](#)
English

Customer View Model
[ENG_CVM_CVM_4-1879023-7_BA.3d_stp.zip](#)

36502C8R2JTDG

High Frequency Inductor, 1008, 8.2 µH, 170 mA, 6 ohm DC Resistance, 5 %, Surface Mount, Taped & Reeled, 2.92 mm [.114 in] Length, Sigma 3650



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
1309350_PASSIVE_COMPONENT

English

Low Inductance, High Frequency Chip Inductors - Type 3650 Series

English