

Scotch[®] ATG 700 Adhesive Transfer Tape System

The power to bond. ATG bond.

scotch" ATC 700

A quick, easy and convenient way to bond just about anything.



Versatility in your hands.

Trusted since 1971, the Scotch[®] ATG 700 Adhesive Transfer Tape System puts portable power in your hands. This small yet mighty system can handle many jobs — faster, cleaner and more conveniently than regular tape.

FASTER

Bond long, large and small surfaces. Finish multiple pieces quicker. No prep time. No cure time.

EASIER

Non-ATG 70

Apply tape on any shape or form, or in uncomfortable positions. Just glide and go!

COST-EFFECTIVE

Refillable applicator. Use only the amount of tape you need. No waste!

SAFER

No harmful vapors or strong odors.

CLEANER

Consistent thickness with no mess from oozing, glue lines or overspray. Liner removes automatically and stays in applicator.

VERSATILE

Choose the right tape for your application and bond anything from paper and wood to metal, glass and hard-to-bond plastics.

CONVENIENT

Complete multiple jobs without reloading. Tape is easy to break off and liner is removed automatically. No electricity or hoses needed.

Dispenses doublesided tape easily on any shaped surface.

Thousands of uses in light and heavy industrial applications.

From appliance and automotive assembly to picture framing, the Scotch[®] ATG 700 Adhesive Transfer Tape System can be used in countless applications for reliable bonding.



Bond light-duty applications.

Scotch[®] ATG Adhesive Transfer Tape 924



Bond heavy-duty applications.

Scotch® ATG Adhesive Transfer Tape 969



S OSHA

Bond in extreme conditions.

Scotch® ATG Adhesive Transfer Tape 926

Bond temporarily.

Scotch[®] ATG Repositionable Double Coated Tissue Tape 928

Scotch[®] ATG 700 System





Scotch® Transfer Tape 926





Scotch® ATG Transfer Tape 976

Product	Thic kness (in mm)	Description	Temperature Resistance		Solvent	Adhesion (1 = low; 10 = very high)		Application Examples
			Short Term (1 hour)	Long Term (Days, Weeks)	Resistance	HSE*	LSE**	
Scotch® ATG Adhesive Transfer Tape 904	0,05	Transparent transfer tape high initial tack and a good price-performance ratio. Provides high shear strenght.	90 °C	70 °C	Medium	6	1	Bonding of scrapbooking, pictures and posters. Attaching of paper, packages and display. General purpose solution. Splicing of Foils (Plastics and tissues)
Scotch® ATG Adhesive Transfer Tape 924EU	0,05	Provides excellent adhesion to most paperstocks for many general purpose needs.	120 °C	85 °C	Medium	5	5	Bond paper folders, packages and displays. Bond mat board and dust covers in picture frames. Splicepaper. Scrapbooking.
Scotch® ATG Adhesive Transfer Tape 926	0,13	Works on a wide variety of substrates and materials,with excellent resistance to solvents and high temperatures.	230 °C	150 °C	High	10	10	Bond appliances, including aluminum foil in kitchen ovens.
Scotch® ATG Repositionable Double Coated Tissue Tape 928	0,05	High tack, low tack and repositionable, it bonds on contact and allows removal and reuse with many papers, foils and films.	65 °C	-	Low	5/1	5/1	Great for bonding temporarily in retail, woodworking, consumergoods, general industrial and more.
Scotch® ATG Adhesive Transfer Tape 969	0,13	Perfect for heavy-dutyneeds. Features high tack and excellent holding power to most plastics, metals, glass and UV-coated paper.	120 °C	80 °C	Medium	8	9	Bond fiberglass/foam layers in resin infusion processes to make composites. Bond automotive, including noise-damping material in auto engine covers. Bond UV-coated point-of-purchase display boxes.
Scotch® ATG Adhesive Transfer Tape 976	0,05	For slightly rough substrates. Features high tack and excellent holding power to most plastics, metals, glass and UV-coated paper.	120 °C	80 °C	Medium	8	9	

*High Surface Energy (HSE) Substrates: Copper, Aluminum, Zinc, Tin, Lead, Stainless Steel, Glass, Porcelain, Polyimide Film, Phenolic, Nylon, Alkyd Enamel, Polyester, Epoxy Paint, Polyurethane Paint, Polycarbonate, PVC Rigid, Acrylic

**Low Surface Energy (LSE) Substrates: PVA, Polystyrene, Acetal, EVA, Polyethylene, Polypropylene, Polyvinyl Fluoride (PVF), Fluoropolymer, Powder-Coated Paint

Please contact your local 3M Sales Representative for details.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Industrial Adhesives and Tapes Division 3M Center, Building 225-3S-06 St. Paul, MN 55144

Phone 800-328-1681 Web 3M.com/ATG