

# 19" CABINETS

## CamRack-LX

Quick Assembly **5 minutes!**

19" Modular cabinets, 600mm wide, designed for cabling, telecommunications, IT and industrial and home installations

- Aluminium profile external structure with diecast high resistance corners.
- 4x19" sections adjustable in depths (gaps of 20mm). Manufactured in steel 2/1,5 mm.
- Front door in safety glass, frame with springswivel hinge and opening angle 190°
- Removable side panels with ¼ turn locks.
- Steel rear door with lock.
- ¼ -turn locking ventilated top panels with cable entries.
- 4 adjustable levelling feet.
- Distributed load capacity: 1.000 Kg (static) / 300 Kg (dynamic)
- Finishes: RAL 7016, Dark grey, anthracite (See below for corner options)



### Glass Front Door

PART NO.	U	WIDTH	DEPTH
CLX126601	12	600mm	600mm
CLX186601	18	600mm	600mm
CLX246601	24	600mm	600mm
CLX306601	30	600mm	600mm
CLX366601	36	600mm	600mm
CLX366801	36	600mm	800mm
CLX426601	42	600mm	600mm
CLX426801	42	600mm	800mm
CLX428601	42	800mm	600mm
CLX428801	42	800mm	800mm

### No Front Door

PART NO.	U	WIDTH	DEPTH
CLX126611	12	600mm	600mm
CLX186611	18	600mm	600mm
CLX246611	24	600mm	600mm
CLX306611	30	600mm	600mm
CLX366611	36	600mm	600mm
CLX366811	36	600mm	800mm
CLX426611	42	600mm	600mm
CLX426811	42	600mm	800mm
CLX428601	42	800mm	600mm
CLX428811	42	800mm	800mm



Red Corners