

Features

Unregulated Converters

- Micro Size SIP4 Package
- 3kVDC Isolation
- Approved for Medical Applications
- Industry Standard Pinout
- Optional Continuous Short Circuit Protected
- UL94V-0 Package Material
- Efficiency to 85 %

Description

The ROM Micro Size DC/DC converter has been designed for isolating or converting DC power rails where board height is at a premium. Although it has a micro-size 7.7mm package, it does not compromise on features and offers a high 3kVDC Isolation, a -40°C to $+85^{\circ}\text{C}$ operating temperature range and optional continuous short circuit protection.

Selection Guide

Part Number SIP4 Micro Size Pack.	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (%)	Max. Capacitive Load ⁽¹⁾
ROM-xx05S	5, 12	5	200	70-78	1000 μF
ROM-xx12S	5, 12	12	83	78-82	470 μF
ROM-xx15S	5, 12	15	66	80-84	470 μF

xx = Input Voltage (other input and output voltage combinations available on request)

* add Suffix "P" for Continuous Short Circuit Protection, e.g. ROM-0505S/P

Specifications (measured at $T_A = 25^{\circ}\text{C}$, nominal input voltage, full load and after warm-up)

Input Voltage Range	$\pm 10\%$	
Output Voltage Accuracy	$\pm 5\%$	
Line Voltage Regulation	1.2%/1% of V_{in} typ.	
Load Voltage Regulation	5V Output	15% max.
(10% to 100% full load)	12V, 15V Output	10% max.
Output Ripple and Noise (20MHz limited)	100mVp-p max.	
Operating Frequency	50kHz min. / 100kHz typ. / 105kHz max.	
Efficiency at Full Load	70% min. / 80% typ.	
Minimum Load = 0%	Specifications valid for 10% minimum load only.	
Isolation Voltage	(tested for 1 second) (rated for 1 minute)	3000VDC 1500VAC / 60Hz
Isolation Capacitance	20pF min. / 75pF max.	
Isolation Resistance	15 G Ω min.	
Short Circuit Protection	1 Second	
P-Suffix	Continuous	
Operating Temperature Range (free air convection)	-40°C to $+85^{\circ}\text{C}$ (see Graph)	
Storage Temperature Range	-55°C to $+125^{\circ}\text{C}$	
Relative Humidity	95% RH	
Package Weight	1g	
Packing Quantity	42 pcs per Tube	
MTBF ($+25^{\circ}\text{C}$)	} Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F 977 x 10^3 hours
($+85^{\circ}\text{C}$)		using MIL-HDBK 217F 189 x 10^3 hours

ECONOLINE

DC/DC-Converter

with 3 year Warranty



1 Watt SIP4 Micro Single Output




E-322406

EN-60950-1 Certified
UL-60950-1 Certified
EN-60601-1 Certified

ROM



Derating-Graph (Ambient Temperature)





Refer to Application Notes

Typical Characteristics



ROM-xx05S



ROM-xx12S



ROM-xx15S



Notes

Note 1 Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.



Certifications

CB Test Report	Report: US/15348/UL	IEC 60950-1:2005 2nd Ed.
UL General Safety	Report: E322406	UL 60950-1 1st Ed.
EN General Safety	Report: PS080804950C2	EN60950-1:2001 + A11:2004
EN Medical safety	Report: ETS-0600068A	EN 60601-1


Package Style and Pinning (mm)

4 PIN SIP Micro Size Package

3rd angle projection



Recommended Footprint Details



RO Pin Connections

Pin #	Single
1	-Vin
2	+Vin
3	-Vout
4	+Vout
XX.X	± 0.5 mm
XX.XX	± 0.25 mm