

Previously known as: Neptune®



Cut



Heat



Medium Duty

Practical, reversible cut-resistant gloves offering advanced durability

- **Heightened defenses:** HyFlex® 70-225 industrial safety gloves' DuPont™ Kevlar® liner helps them achieve ANSI A3/ISO D cut-resistant glove levels
- **Added practicality:** HyFlex® 70-225 safety gloves' launderable, reversible design means they can be repeatedly washed and worn on either hand, for reduced replacement costs and extra convenience
- **Specialized protection:** These PPE gloves' terry loop weave grants their liner heat insulation capabilities, preventing workplace injuries
- **Improved durability:** HyFlex® 70-225 industrial gloves are abrasion-resistant, with a reinforced thumb welt and EN and ANSI level 3 abrasion protection
- **Elevated comfort:** Their thick liner provides shock absorption, for genuinely comfortable hand protection with a cushioned fit



Industries

- Automotive
- Machinery and Equipment

Applications

- Metalworking & assembly operations
- Chassis assembly, body trimming
- Seizing structural and body parts
- Inspection (picking, checking and marking)
- Touching up
- Welding

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

70-225

Medium duty cut resistant gloves

Previously known as: Neptune[®]

Key Features

- **DuPont™ Kevlar[®] liner:** PPE gloves with ANSI A3/ISO D cut protection
- **Launderable design:** Washable and reusable, for added practicality
- **Reinforced thumb welt:** EN and ANSI level 3 abrasion protection

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



144XD

EN 407



2122XX



0493

Technologies

Kevlar[®]

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex [®] 70-225	Liner Material: Kevlar [®] Cuff Style: Knitwrist	7	6, 7, 8, 9	230-280 mm/ 8.22-10.63 inches	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell