

Product datasheet

Specifications



Kaedra - for modular device - 1 x 18 modules - 2 terminal blocks

Local distributor code:

391264474

13432

EAN Code: 3303430134329

Main

Range	Mureva
Product name	Mureva Enclosure
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for modular device
Mounting plate description	Without mounting plate

Complementary

Enclosure mounting	Surface
9 mm pitches	36
Number of 18 mm modules per row	18
Total number of 18 mm modules	18
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Provided equipment	1 marking kit 1 wiring strap 1 terminal block support 2 terminal block 16 holes
Type of front cover	Transparent Reversible
Power dissipation in W	34 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	17
Number of terminal blocks	2 earth / neutral (screw connection) with 16 outgoing
Distribution block outgoing	16 x 10 mm ² 16 x 16 mm ²
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	448 mm
Height	280 mm
Depth	160 mm
Internal depth	88 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60670-1 IEC 60670-24 EN 50262 IEC 60695-2-1
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.500 cm
Package 1 Width	29.000 cm
Package 1 Length	46.500 cm
Package 1 Weight	2.717 kg
Unit Type of Package 2	X12
Number of Units in Package 2	36
Package 2 Height	116.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	109.800 kg

Logistical informations

Country of origin	IT
--------------------------	----

Contractual warranty

Warranty (in months)	18
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint 15

Environmental Disclosure [Product Environmental Profile](#)

Use Better



Materials and Substances

Average percentage of recycled plastic content 24 %

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number 5305d5d6-3783-4b3d-abd0-61fa4a6023d7

REACH Regulation [REACH Declaration](#)

Halogen-free status Halogen free plastic parts product

Use Longer



Lifetime extension

Repair No

Use Again



Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

Technical Illustration

Exploded view

