

R10-E2Z4-V15.0K

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield R10


TE Internal #: 4-1393767-4

General Purpose Signal Relay, DC, Monostable, 4 Form C 4PDT-CO, 2 A Contact Rating, 115 VDC Coil Voltage, Potter & Brumfield R10

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Signal Relay**

Current Type: **DC**

Coil Magnetic System: **Monostable**

Contact Arrangement: **4 Form C 4PDT-CO**

Contact Current Rating: **2 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Signal Relay
------------------------	------------------------------

Configuration Features

Contact Special Features	Bifurcated/Twin Contacts
Contact Number of Poles	4
Coil Special Features	Sensitive Version
Contact Arrangement	4 Form C 4PDT-CO

Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts	500 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	1000 Vrms
Contact Switching Load (Min)	1mA @ 12V
Coil Resistance	15000 Ω
Insulation Initial Resistance	10000 MΩ
Contact Current Rating	2 A
Coil Voltage Rating	115 VDC
Contact Voltage Rating	120 VAC
Coil Power Rating DC	.9 W
Insulation Initial Dielectric Between Contacts & Coil	1000 Vrms

Body Features

--	--



Product Weight	40 g[1.41 oz]
Enclosure Type	Dust Protected

Contact Features

Contact Material	Ag
------------------	----

Termination Features

Main Termination & Connection Type	Solder Pins
Coil Termination & Connection Type	Solder Pins

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Dimensions

Product Width	18.66 mm[.734 in]
Product Length	24.13 mm[.95 in]
Product Height	29.97 mm[1.17 in]

Usage Conditions

Operating Temperature Range	-55 – 75 °C[-67 – 167 °F]
Environmental Category of Protection	RTI
Environmental Ambient Temperature (Max)	75 °C[167 °F]

Operation/Application

Current Type	DC
Coil Magnetic System	Monostable

Packaging Features

Packaging Method	Package
------------------	---------

Other

Coil Power Rating Class	.8 – 1 W
Contact Current Class	16 A
Environmental Ambient Temperature Class	70 – 85 °C
Height Class (Mechanical)	30 – 40 mm
Length Class (Mechanical)	20 – 25 mm
Width Class (Mechanical)	16 – 20 mm

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.7% in 74019106) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 7-1393766-8  
R10-E1Z4-V15.0K=R10

Also in the Series | [Potter & Brumfield R10](#)



Board-to-Board Headers & Receptacles(1)



PCB Headers & Receptacles(1)



PCB Relays(28)



Relay Accessories(27)

Customers Also Bought

TE Part #DRC16-70SBE-P013UK  
PLG, 70P, BLK, E, SEAL BOND, B

TE Part #SRK-PC-080-25-601  
PIN, SOLID, SIZE M8, 25mm2, AG

TE Part #K1008699  
Relay 26-60-05

TE Part #CAT-H396-CH8172  
DEUTSCH HDP20 Housings

TE Part #K1002956  
Toggle Switch 08-4-1-13

TE Part #K1007153  
Toggle Switch 08-1-1-13

TE Part #DTT-20-03  
CRIMP TOOL

TE Part #K1060489  
Relay 29-113-12

TE Part #2-2176245-2  
CRGS1206 5% 56R

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG\_CVM\_CVM\_4-1393767-4\_A.2d\_dxf.zip
- English
- Customer View Model
- ENG\_CVM\_CVM\_4-1393767-4\_A.3d\_igs.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1393767-4\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[R10 General Purpose Dry Circuit to 7.5 Amp Multicontact AC or DC Relay](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[CSA Certificate](#)

English