

## pneumatic valve VL-5/2-D-2-C Part number: 151845

**FESTO** 

5/2-way function, pneumatically actuated, with spring return





## **Data sheet**

Feature	Value
Valve function	5/2 monostable
Type of actuation	pneumatic
Width	54 mm
Standard nominal flow rate	2,300 l/min
Operating pressure	2 16 bar
Design structure	Piston slide
Type of reset	Air spring
Authorisation	UL - Recognized (OL)
Maritime classification	see certificate
Nominal size	11.5 mm
Grid dimension	56 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Conforms to standard	ISO 5599-1
Manual override	None
ISO code	202
Type of piloting	direct
Flow direction	non reversible
Overlap	Positive overlap
Pilot pressure	2 16 bar
Switching time off	39 ms
Switching time on	23 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Vibration resistance	Transport application test at severity level 1 in accordance with FN
	942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN
	60068-2-27
Medium temperature	-10 60 °C
Sound pressure level	85 dB(A)
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-10 60 °C
Product weight	550 g
Mounting type	On sub-base
	With through-hole and screw
Pilot air port 14	Connection plate size 2 as per ISO 5599-1
Pneumatic connection, port 1	Connection plate size 2 as per ISO 5599-1
Pneumatic connection, port 2	Connection plate size 2 as per ISO 5599-1
Pneumatic connection, port 3	Connection plate size 2 as per ISO 5599-1
Pneumatic connection, port 4	Connection plate size 2 as per ISO 5599-1
Pneumatic connection, port 5	Connection plate size 2 as per ISO 5599-1
Materials note	Conforms to RoHS
Material seals	HNBR
	NBR
Material housing	Aluminium die cast