



SIGNAL CONVERTER 24-240 V AC/DC, 3-WAY  
 ISOLATION IN: 0-60MV, 0-100MV, 0-300MV, 0-500MV,  
 0-1V, 0-2V, 0-5V, 0-10 0-20V, 2-10V, 0-5MA, 0-10MA,  
 0-20MA, 4-20MA, +5MA, +-20MA OUT: 0 TO 10 V, 0/4  
 TO 20 MA SPRING-TYPE TERMINAL

Figure similar

product brandname		SIRIUS
Product designation		universal converter
Design of the product		Switchable universal converters, active

General technical data		
Consumed active power	W	0.5
Insulation voltage for overvoltage category III according to IEC 60664		
• with degree of pollution 3 rated value	V	300
Type of voltage		AC/DC
Shock resistance acc. to IEC 60068-2-27		sinusoidal half-wave 15g / 11 ms
Vibration resistance acc. to IEC 60068-2-6		6 ... 150 Hz: 2 g
Surge voltage resistance rated value	V	4 000
Protection class IP		IP20
Equipment marking		
• acc. to DIN EN 81346-2		T
• acc. to DIN EN 61346-2		K
Display version LED		Yes
Relative metering precision	%	0.1

Relative linearity deviation	%	0.05
Temperature drift per °C	%/°C	0.015
Number of channels		1
Voltage ripple maximum	mV	20
Limit frequency	Hz	30
Settling time for 1 % deviation	ms	17
Rise time	ms	6

#### Inputs/ Outputs

Type of signal at input		0 ... 60 mV, 0 ... 100 mV, 0 ... 300 mV, 0 ... 500 mV, 0 ... 1 V, 0 ... 2 V, 0 ... 5 V, 0 ... 10 V, 0 ... 20 V, 2 ... 10 V, 0 ... 5 mA, 0 ... 10 mA, 0 ... 20 mA, 4 ... 20 mA, +/-5 mA, +/-20 mA
Input voltage	V	30
• maximum		
Type of signal at output		0 ... 10 V, 0 ... 20 mA, 4 ... 20 mA
Property of the output Short-circuit proof		Yes
Load		
• at voltage output maximum	kΩ	2
• at the current output maximum	Ω	500

#### Supply voltage

Supply voltage		
• at AC at 50 Hz rated value	V	24 ... 240
• at AC at 60 Hz rated value	V	24 ... 240
• at DC rated value	V	24 ... 240
Supply voltage frequency rated value	Hz	50 ... 60
Operating range factor supply voltage rated value		
• at AC at 50 Hz		0.8 ... 1.1
• at AC at 60 Hz		0.8 ... 1.1
• at DC		0.8 ... 1.1

#### Electromagnetic compatibility

EMC emitted interference acc. to IEC 60947-1		Environment B
EMI immunity acc. to IEC 60947-1		corresponds to degree of severity 3
Field-bound parasitic coupling acc. to IEC 61000-4-3		0.8 ... 1 GHz 10 V/m, 1.4 ... 2 GHz 3 V/m, 2 ... 2.7 GHz 1 V/m
Conducted interference		
• due to conductor-conductor surge acc. to IEC 61000-4-5		1 kV
• due to burst acc. to IEC 61000-4-4		1 kV 5/50 ns
Electrostatic discharge acc. to IEC 61000-4-2		6 kV contact discharge / 8 kV air discharge

#### Galvanic isolation

Design of the electrical isolation		3 paths
Galvanic isolation		

• between entrance and outlet	Yes
• between the outputs	No
• between the inputs	No
• between the voltage supply and other circuits	Yes

### Connections/Terminals

<b>Type of electrical connection</b>		spring-loaded terminals
<b>Type of connectable conductor cross-sections</b>		
• solid		1x (0.25 ... 2.5 mm <sup>2</sup> )
• finely stranded with core end processing		1x (0.25 ... 1.5 mm <sup>2</sup> )
• finely stranded without core end processing		1x (0.25 ... 2.5 mm <sup>2</sup> )
• at AWG conductors solid		1 x (20 ... 14)
• at AWG conductors stranded		1x (20 ... 14)
<b>Connectable conductor cross-section</b>		
• solid	mm <sup>2</sup>	0.25 ... 2.5
• finely stranded with core end processing	mm <sup>2</sup>	0.25 ... 1.5
• finely stranded without core end processing	mm <sup>2</sup>	0.25 ... 2.5
<b>AWG number as coded connectable conductor cross section</b>		
• stranded		20 ... 14
• solid		20 ... 14

### Installation/ mounting/ dimensions

<b>Mounting position</b>		any
<b>Mounting type</b>		snap-on mounting
<b>Height</b>	mm	93
<b>Width</b>	mm	17.5
<b>Depth</b>	mm	72.5
<b>Required spacing</b>		
• with side-by-side mounting		
— forwards	mm	0
— Backwards	mm	0
— upwards	mm	0
— downwards	mm	0
— at the side	mm	0
• for grounded parts		
— forwards	mm	0
— Backwards	mm	0
— upwards	mm	0
— downwards	mm	0
— at the side	mm	0
• for live parts		
— forwards	mm	0

— Backwards	mm	0
— upwards	mm	0
— downwards	mm	0
— at the side	mm	0

#### Ambient conditions

<b>Installation altitude at height above sea level maximum</b>	m	2 000
<b>Ambient temperature</b>		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +80
• during transport	°C	-40 ... +80
<b>Relative humidity during operation</b>	%	10 ... 95

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RS7006-2FW00>

##### Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RS7006-2FW00>


##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RS7006-2FW00>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RS7006-2FW00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RS7006-2FW00&lang=en)





last modified:

04/30/2017