

## PLT8LH-L0



- Greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- Versatile cable ties can be used in countless applications
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry
- Curved tip on Standard cross section is easy to pick up from flat surfaces and allows faster initial threading to speed installation. Light-Heavy and Heavy cross section is a straight tip design

■ Part Number	PLT8LH-L0
■ RoHS Compliancy Status	Compliant
■ Part Description	Cable Tie, 27.6", Light-Heavy cross section
■ Product Type	Cable Ties
■ Material	Weather Resistant Nylon 6.6
■ Color	Black
■ CSA Certified	No
■ UL Listed (File #E56854)	No
■ UL Recognized (File #E56854)	No
■ Length (In.)	27.6
■ Length (mm)	701
■ Width (In.)	.300
■ Width (mm)	7.6
■ CE Compliant	Yes
■ Cross Section	Light-Heavy
■ Head Height (In.)	.325
■ Head Height (mm)	8.3
■ Head Width (In.)	.480
■ Head Width (mm)	12.2
■ Locking Style	Locking
■ Material Flammability Rating	UL 94-HB
■ Max. Bundle Diameter (In.)	8.00
■ Max. Bundle Diameter (mm)	203
■ Max. Continuous Use Temperature	185°F (85°C)
■ Min. Loop Tensile Strength (Lbs.)	120
■ Min. Loop Tensile Strength (N)	534

■ Pricing Description	Cable Tie, 27.6"L (701mm), Light-Heavy, Weather Resistant, Black
■ Thickness (In.)	.075
■ Thickness (mm)	1.9
■ Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
■ Min. Order UOM	PC
■ Min. Order Qty.	50
■ BOM Qty. (# of Pkgs.)	

