



## Slotted Grommet, Black, PE, 3.7mm Max Panel, 30.5m L, PK1

GEE144F-A-C0

The GEE144F-A-C0 Polyethylene Slotted Grommet Edging protects and prevents wires and cables from chafing against sharp edges of panel walls and knockouts. Slotted edging is recommended for use on irregularly shaped and round panel holes. The material is highly flexible, while the adhesive lining ensures the product will stay in place. Packaged on a 100' (30.5m) reel for easy handling and dispensing. Polyethylene. Designed for 0.099"-0.144" (2.5 mm-3.7 mm) thick panels. Color Black. 1 per package.

### Specifications

Note	Designed for irregular shaped or round panel holes
Product Type	Slotted Grommet Edging
Color	Black
Material	Polyethylene
Maximum Compatible Panel Thickness (In.)	0.14
Maximum Compatible Panel Thickness (mm)	3.7
Minimum Compatible Panel Thickness (In.)	0.099
Minimum Compatible Panel Thickness (mm)	2.5
Maximum Operating Temperature (°C)	50
Maximum Operating Temperature (°F)	122
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Overall Length (ft.)	100
Overall Length (m)	30.48
Overall Width (In.)	0.21
Overall Width (mm)	5.4
Overall Height (In.)	0.22
Overall Height (mm)	5.6
Resistance Properties	Weather-Resistant
Standards Met	RoHS Compliant
Application	To Protect and Prevent Wires and Cables from Chafing Against Sharp Edges of Panel Walls and Knockouts.
Part Features	Provides protection for cables being installed where there might be sharp edges with irregular shaped and round panel holes.

**Packaging Detail**

UPC	07498362717
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.3169
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000