




SFP28

TE Internal #: 1-2007492-6

SFP+, Cage Assembly with Integrated Connector, .8mm [.032in]
Centerline, Signal, Operating Temperature Range -55 – 105 °C [-67 – 221 °F]

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP+ Stacked Cage Assemblies



Form Factor: SFP+
Pluggable I/O Product Type: Cage Assembly with Integrated Connector
Centerline (Pitch): .8 mm [.032 in]
Sealable: No
Circuit Application: Signal

[All SFP+ Stacked Cage Assemblies \(73\)](#)

Features

Product Type Features

Cage Type	Stacked
Form Factor	SFP+
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Sealable	No

Configuration Features

Number of Positions	40
Number of Ports	2
Port Matrix Configuration	2 x 1

Electrical Characteristics

Data Rate (Max)	16 Gb/s
-----------------	---------

Contact Features

Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
--------------------------------------	--



Tail Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 µm

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	3 mm[.118 in]

Housing Features

Cage Material	Nickel Silver
Centerline (Pitch)	.8 mm[.032 in]

Dimensions

PCB Thickness (Recommended)	1.5 mm[.059 in]
-----------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	EMI Enhanced
Heat Sink Compatible	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247)



Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2821033-8 QSFP TO [4]SFP+, 28G, 1M, 33AWG	 TE Part # 2142970-6 CABLE ASSY, MICRO SFP+ TO STD SFP+, 5M	 TE Part # 2142970-5 CABLE ASSY, MICRO SFP+ TO STD SFP+, 4M	 TE Part # CAT-C11-H506 SFP+ to SFP+ I/O Cable Assembly: 26 AWG
 TE Part # CAT-C11-H5 SFP+ to SFP+ I/O Cable Assembly: 24 AWG	 TE Part # CAT-C11-H50626 SFP+ to SFP+ I/O Cable Assembly: 30 AWG	 TE Part # 2142970-1 CABLE ASSY, MICRO SFP+ TO STD SFP+, 0.5M	 TE Part # 4-2334985-2 SFP56 DIRECT ATTACH CA, 1M, 32AWG
 TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG	 TE Part # 2142970-7 CABLE ASSY, MICRO SFP+ TO STD SFP+, 6M	 TE Part # 4-2821222-5 SFP56 DIRECT ATTACH CA, 2M, 30AWG	 TE Part # 2142970-3 CABLE ASSY, MICRO SFP+ TO STD SFP+, 2M



TE Part # CAT-Q17-N490333
QSFP56-Four SFP56 Cable Assembly:
26 AWG



TE Part # CAT-C11-N490333
QSFP28-Four SFP+ Cable Assembly:
30 AWG



TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly:
26 AWG



TE Part # CAT-C11-H5062
SFP+ to SFP+ I/O Cable Assembly: 28
AWG



TE Part # 2142970-2
CABLE ASSY, MICRO SFP+ TO STD
SFP+, 1M



TE Part # 2334985-2
SFP28 DIRECT ATTACH CA, 1M,
32AWG




TE Part # 2142970-4
CABLE ASSY, MICRO SFP+ TO STD
SFP+, 3M



TE Part # 4-2821224-5
SFP56 DIRECT ATTACH CA, 3M,
26AWG

Customers Also Bought




TE Part #2291931-2
CDFP RCPT CONNECTOR & CAGE
STYLE 1



TE Part #1551920-2
zQSFP+ connector assembly




TE Part #5177986-2
0.8FH,P05H.5,060,08/Sn,TR,SC




TE Part #5-2170703-4
CAGE ASSEMBLY, QSFP28 1X1,
SPRING



TE Part #2227670-1
zQSFP+ STACKED RECEPTACLE
ASSEMBLY 2X2



TE Part #5532600-2
CONN SEC II 25 POS 100 C/L RA



TE Part #1551920-7
ZQSFP+ CONNECTOR ASSEMBLY



TE Part #1934301-1
TinMan header Assy 3x8 Right



TE Part #1645621-1
HM ZD 4 PAIR PIN ASSEM, 15 col 5.3
Sn



TE Part #2-2354329-1
CAGE ASSY, QSFP28, 1X2,ZIP HSK, LP

Documents



Product Drawings

SFP+assy2x1 EMI Sprg Inner LP Sn Enhance

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2007492-6_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2007492-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2007492-6_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English