



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Ergocrimp Hand Tool Assembly or Die

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (.35% in Component Part)











Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 368376-1 81P REC HSG ASSY(SIEMENS) BLK	 TE Part # CAT-M8793-T273 MQS, RECEPTACLE AND TAB	 TE Part # 1-2325634-1 2POS,PCON12,HDR INNER HSG ASSY, COD NEUT	 TE Part # 2-2310224-1 2POS,PCON12,HDR ASSY,COD A,S.V. COD NEUT
 TE Part # 2-2325634-1 2POS,PCON12,HDR INNER HSG ASSY, COD NEUT	 TE Part # 2208304-1 8POS MQS REC	 TE Part # 2208304-2 8POS,MQS,REC HSG,WITH SB,ASSY	 TE Part # 2294399-1 4POS MQS REC COD A
 TE Part # 2294399-3 4POS,MQS,REC HSG,WITH CPA,ASSY	 TE Part # 2294399-5 4POS,MQS,REC HSG,WITH CPA,ASSY	 TE Part # 2322637-1 12POS,MQS,REC HSG,UNSLD	 TE Part # 2322637-2 12POS,MQS,REC HSG,UNSLD



TE Part # 2329592-2
20POS,MQS,REC HSG,UNSLD

TE Part # 3-2325634-1
2POS,PCON12,HDR INNER HSG ASSY, COD NEUT

TE Part # 5-963726-1
MQS SOCKET CONTACT

TE Part # 6-2325634-1
2POS,PCON12,HDR INNER HSG ASSY, COD NEUT

TE Part # 6-928918-3
MQS0,63 Ag tab LL unseal. 0,2-0,35

TE Part # 1-963725-1
MQS PIN CONTACT

TE Part # 963730-1
MQS PIN CONTACT WITH SPRING

TE Part # 2112668-1
23POS MIXED MQS REC

Customers Also Bought

TE Part #6-1625890-1
2W SM M/OX 5% 56R

TE Part #6-1625890-6
2W SM M/OX 5% 68R

TE Part #4-2176412-1
5W XSM M/OX 5% 240R

TE Part #2-2176412-2
5W XSM M/OX 5% 39R

TE Part #1-963539-2
18pos MQS .63 header 90deg

TE Part #1614894-7
CPF 0805 196K 0.1% 25PPM 1K RL

TE Part #4-1579001-6
ERGO DIE MCP 1,2 LL EDS

TE Part #539685-2
ERGO DIE MQS

TE Part #539951-2
ERGO DIE MCP 2,8K

Documents



Product Drawings

ERGOCRIMP DIE SET MQS

German

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

German