



NO.1121030704

检 测 报 告

Test Report

样品名称： 可充电单电芯电池 602040 3.7V 450mAh 1.665Wh

Name of Sample: /

委托单位： 深圳市格莱德电子有限公司

Consignor: /



上海化工院检测有限公司

Shanghai Institute of Chemical Industry Testing Co., Ltd.

上海化工院检测有限公司 检测报告

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1121030704

1/11

样品名称 Name of Sample	中文 Chinese	可充电单电芯电池 602040 3.7V 450mAh 1.665Wh		
	英文 English			
样品编号 Sample No.	1121030704			
委托单位 Consignor	深圳市格莱德电子有限公司			
生产单位 Manufacturer	深圳市格莱德电子有限公司			
检测方法 Test method	联合国《关于危险货物运输的建议书 试验和标准手册》 ST/SG/AC.10/11/Rev.6 Amend.1 38.3 UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3			
判定标准 Criterion	联合国《关于危险货物运输的建议书 试验和标准手册》 ST/SG/AC.10/11/Rev.6 Amend.1 38.3 UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3			
样品外观 Appearance	银色, 黄色双色 铝塑外壳 Silvery and yellow Aluminum-plastics shell			
样品接受日期 Accepted Date	2021-03-25	检测起迄日期 Test Date	2021-04-13 ~ 2021-05-12	
检测项目 Test Items	高度模拟; 热测试; 振动; 冲击; 外短路; 挤压; 过充电; 强制放电 Altitude simulation, Thermal test, Vibration, Shock, External short circuit, Crush, Overcharge, Forced discharge			
检测结论 Conclusion	经检测, 该样品符合联合国《关于危险货物运输的建议书 试验和标准手册》 ST/SG/AC.10/11/Rev.6 Amend.1 38.3标准要求。 The sample has passed the test items of UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 38.3 生效日期(Date): 2021-05-12			
备注 Comment	可充电单电芯电池 Rechargeable Single Cell Battery. /			
委托单位地址 Consignor Address			邮政编码 Post Code	518100

批准
Approver:
职务
Title:

王宗

副总工程师 (Vice chief engineer)

审核
Checker:

陈建峰

编制
Compiler:

傅建



上海化工院检测有限公司 检测报告

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1121030704

2/11

序号 No.	检测项目名称 Name of Test Items	标准要求或标准条款号 Standard requirement or The Clause Number of Standard	检测结果 Test Result	本项结论 Conclusion	备注 Remark
1	高度模拟 Altitude simulation	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.1 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.1	见附表 1 See Appendix 1	合格 Passed	/
2	热测试 Thermal test	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.2 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.2	见附表 2 See Appendix 2	合格 Passed	/
3	振动 Vibration	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.3	见附表 3 See Appendix 3	合格 Passed	/
4	冲击 Shock	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.4 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.4	见附表 4 See Appendix 4	合格 Passed	/
5	外短路 External short circuit	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.5 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.5	见附表 5 See Appendix 5	合格 Passed	/
6	挤压 Crush	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.6 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.6	见附表 6 See Appendix 6	合格 Passed	/
7	过充电 Overcharge	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.7 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.7	见附表 7 See Appendix 7	合格 Passed	/
8	强制放电 Forced discharge	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.8 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.8	见附表 8 See Appendix 8	合格 Passed	/
检测环境条件 Test Environment Condition		环境温度:22℃-23℃;环境湿度:/% Ambient temperature:22℃-23℃;Ambient humidity:/%			
分包检验情况 Subcontracted Test Condition		检测项目 Test Item	/		
		分包实验室 Subcontracted Laboratory	名称 Name	/	邮编 Post Code
			地址 Address	/	电话 Tel

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 1

3/11

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 2

4/11

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 3

5/11

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

[illegible]

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 5

7/11

序号 No.	5	检测项目名称 Name of Test Items	外短路 External short circuit
样品编号 Sample No.	样品状态 Sample Status	样品表面最高温度 Max. External Temperature /℃	其他现象 Other Event
001	1CYC完全充电 1CYC Fully charged	57.2	O
002	1CYC完全充电 1CYC Fully charged	56.9	O
003	1CYC完全充电 1CYC Fully charged	57.9	O
004	1CYC完全充电 1CYC Fully charged	56.8	O
005	1CYC完全充电 1CYC Fully charged	56.7	O
006	25CYC完全充电 25CYC Fully charged	57.5	O
007	25CYC完全充电 25CYC Fully charged	57.2	O
008	25CYC完全充电 25CYC Fully charged	56.5	O
009	25CYC完全充电 25CYC Fully charged	56.8	O
010	25CYC完全充电 25CYC Fully charged	56.9	O
以下空白	This space intentionally left blank		

备注：D-解体 R-破裂 F-起火 O-无解体、无起火、无破裂。

Note: D-Disassembly R-Ruptur F-Fire O-No Disassembly,No Fire & No Rupture.

检测报告-附表6

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 6

NO. 1121030704

8/11

序号 No.	6	检测项目名称 Name of Test Items	挤压 Crush
样品编号 Sample No.	样品状态 Sample Status	样品表面最高温度 Max. External Temperature / °C	其他现象 Other Event
011	1CYC 50%容量 1CYC 50% Capacity	20.4	O
012	1CYC 50%容量 1CYC 50% Capacity	20.5	O
013	1CYC 50%容量 1CYC 50% Capacity	20.5	O
014	1CYC 50%容量 1CYC 50% Capacity	20.5	O
015	1CYC 50%容量 1CYC 50% Capacity	20.6	O
016	25CYC 50%容量 25CYC 50% Capacity	20.5	O
017	25CYC 50%容量 25CYC 50% Capacity	20.5	O
018	25CYC 50%容量 25CYC 50% Capacity	20.5	O
019	25CYC 50%容量 25CYC 50% Capacity	20.5	O
020	25CYC 50%容量 25CYC 50% Capacity	20.5	O
以下空白	This space intentionally left blank		

备注：D-解体 F-起火 O-无解体、无起火。

Note: D-Disassembly F-Fire O-No Disassembly & No Fire.

检测报告-附表7

NO. 1121030704

9/11 .

[illegible]

上海化工院检测有限公司
检测报告-附表8
Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 8

NO. 1121030704


10/11

序号 No.	8	检测项目名称 Name of Test Items	强制放电 Forced discharge
样品编号 Sample No.	样品状态 Sample Status	其他现象 Other Event	
029	1CYC完全放电 1CYC Fully discharged	O	
030	1CYC完全放电 1CYC Fully discharged	O	
031	1CYC完全放电 1CYC Fully discharged	O	
032	1CYC完全放电 1CYC Fully discharged	O	
033	1CYC完全放电 1CYC Fully discharged	O	
034	1CYC完全放电 1CYC Fully discharged	O	
035	1CYC完全放电 1CYC Fully discharged	O	
036	1CYC完全放电 1CYC Fully discharged	O	
037	1CYC完全放电 1CYC Fully discharged	O	
038	1CYC完全放电 1CYC Fully discharged	O	
039	25CYC完全放电 25CYC Fully discharged	O	
040	25CYC完全放电 25CYC Fully discharged	O	
041	25CYC完全放电 25CYC Fully discharged	O	
042	25CYC完全放电 25CYC Fully discharged	O	
043	25CYC完全放电 25CYC Fully discharged	O	
044	25CYC完全放电 25CYC Fully discharged	O	
045	25CYC完全放电 25CYC Fully discharged	O	
046	25CYC完全放电 25CYC Fully discharged	O	
047	25CYC完全放电 25CYC Fully discharged	O	
048	25CYC完全放电 25CYC Fully discharged	O	
备注: D-解体 F-起火 O-无解体、无起火。 Note: D-Disassembly F-Fire O-No Disassembly & No Fire.			

上海化工院检测有限公司
检测报告-附图
Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix

NO. 1121030704

11/11



报告结束