

E/P pressure regulator, Series ED05

R414002297


Series
ED05

2025-05-09

- Tailored, on-demand pressure control
- Robust poppet valve technology guarantees a long service life
- High flow for a wide range of tasks
- Highly dynamic direct acting technology
- No wearable pilot valves or diaphragm
- Various electrical connection options

Series ED05

The AVENTICS ED05 direct-acting pressure regulator ensures sensitive pressure control by combining digital control electronics with innovative proportional technology. The robust poppet valve technology, a large opening cross-section and the use of a soft-sealing valve seat make the valve highly resistant to contamination.



Technical data

Type	Potentiometer control without actual output value
Control	Directly controlled
Control	Analog
Function	Air exhaust
Output signal	Switch output
Operational voltage DC	24 V
Nominal input value	0 ... 10 V
Min. regulation range	0 bar
Max. regulation range	10 bar
Min. working pressure	0 bar
Max. working pressure	11 bar
Hysteresis	< 0,06 bar
Medium	Compressed air
Nominal flow Qn	1000 l/min
Min. ambient temperature	0 °C
Max. ambient temperature	70 °C
Min. medium temperature	0 °C
Max. medium temperature	70 °C
Protection class	IP65

E/P pressure regulator, Series ED05

R414002297

Series

ED05

2025-05-09

Permissible ripple	5%
Max. particle size	50 µm
Min. oil content of compressed air	0 mg/m ³
Max. oil content of compressed air	1 mg/m ³
Type	Poppet valve
Mounting orientation	$\alpha = 0-90^\circ$ $\beta = 0-90^\circ$
Certificates	CE declaration of conformity
Compressed air connection input	G 1/4
Compressed air connection output	G 1/4
Compressed air connection, exhaust	G 1/4
Electrical connection size	via signal connection
Signal connection	input and output
Signal connection	Plug
Signal connection	M12
Signal connection	5-pin
Industry	Industrial
Weight	0.95 kg

Material

Housing material	Die-cast aluminum Steel, chrome-plated
Seal material	Hydrogenated acrylonitrile butadiene rubber
Part No.	R414002297

Technical information

With oil-free, dry air, other installation positions are possible on request.

The protection class is only ensured when the plug is mounted properly. For detailed information, see operating instructions.

The min. control pressure must be adhered to, since otherwise faulty switching and valve failure may result!

The pressure dew point must be at least 15 °C less than ambient and medium temperature and may not exceed 3 °C.

The oil content of compressed air must remain constant during the life cycle.

Use only the approved oils from AVENTICS. Further information can be found in the "Technical information" document (available in <https://www.emerson.com/en-us/support>).

E/P pressure regulator, Series ED05


R414002297

Series

ED05

2025-05-09

Dimensions




1) Core hole 15 mm deep for self-tapping screws M6

2) Universal threaded connection, suitable for G1/4 according to ISO 228/1:2000 and 1/4-27 NPTF

3) Through hole

Functional diagram




a) Nominal input value b) Actual output value The E/P pressure control valve modulates the pressure corresponding to an analog electrical nominal input value.

1) Operating pressure

2) Working pressure

3) Exhaust

Functional diagram for switch output (acknowledge signal)





a) Nominal input value c) Switch output (acknowledge signal) The E/P pressure control valve modulates the pressure corresponding to an analog electrical nominal input value.

1) Operating pressure

2) Working pressure

3) Exhaust

Characteristic and pin assignment for current and voltage control with actual output value




1) Operational voltage

2) Nominal value (pin 2) and switch output (pin 4) are related to 0 V. Acknowledge signal

3) The operating voltage must be protected by an external M 1.6 A fuse.

Durchflussdiagramm für Druckbereich bis 10 bar



P_v = Supply pressure

Connect the plug via a shielded cable to ensure EMC