

# Servo motor EMMT-AS-40-S-LS-R2M

Part number: 8171413

**FESTO**



 General operating condition

## Data sheet

| Feature                                                   | Value                                                                                      |
|-----------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Ambient temperature                                       | -40 °C ... 40 °C                                                                           |
| Note on ambient temperature                               | Up to 80°C with derating -2%/°C                                                            |
| Max. installation height                                  | 4000 m                                                                                     |
| Note on max. installation height                          | As of 1,000 m: only with derating of -1.0% per 100 m                                       |
| Storage temperature                                       | -40 °C ... 70 °C                                                                           |
| Relative air humidity                                     | 0 - 90%                                                                                    |
| Conforms to standard                                      | IEC 60034                                                                                  |
| Temperature class as per EN 60034-1                       | F                                                                                          |
| Max. winding temperature                                  | 155 °C                                                                                     |
| Rating class as per EN 60034-1                            | S1                                                                                         |
| Temperature monitoring                                    | Digital motor temperature transmission via EnDat® 2.2                                      |
| Motor type to EN 60034-7                                  | IM V1<br>IM V3                                                                             |
| Mounting position                                         | Any                                                                                        |
| Degree of protection                                      | IP40                                                                                       |
| Note on degree of protection                              | IP67 for motor housing including connection components                                     |
| Concentricity, coaxiality, axial runout to DIN SPEC 42955 | N                                                                                          |
| Balance quality                                           | G 2.5                                                                                      |
| Detent torque                                             | <1.0% of peak torque                                                                       |
| Bearing lifetime under nominal conditions                 | 20000 h                                                                                    |
| Interface code, motor out                                 | 40P                                                                                        |
| Electrical connection 1, connection type                  | Hybrid plug                                                                                |
| Electrical connection 1, connector system                 | M23x1                                                                                      |
| Electrical connection 1, number of connections/cores      | 15                                                                                         |
| Electrical connection 1, connection pattern               | 00995913                                                                                   |
| Pollution degree                                          | 2                                                                                          |
| Note on materials                                         | RoHS compliant                                                                             |
| Corrosion resistance class CRC                            | 0 - No corrosion stress                                                                    |
| LABS (PWIS) conformity                                    | VDMA24364 zone III                                                                         |
| Vibration resistance                                      | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6           |
| Shock resistance                                          | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                          |
| Approval                                                  | RCM<br>c UL us - Recognised (Oil)                                                          |
| CE mark (see declaration of conformity)                   | To EU EMC Directive<br>To EU Low Voltage Directive<br>In accordance with EU RoHS Directive |

| Feature                                                     | Value                                                                 |
|-------------------------------------------------------------|-----------------------------------------------------------------------|
| UKCA marking (see declaration of conformity)                | To UK RoHS instructions<br>To UK regulations for electrical equipment |
| Certificate issuing authority                               | UL E342973                                                            |
| Nominal operating voltage DC                                | 325 V                                                                 |
| Type of winding switch                                      | Star inside                                                           |
| Number of pole pairs                                        | 5                                                                     |
| Standstill torque                                           | 0.24 Nm                                                               |
| Nominal torque                                              | 0.21 Nm                                                               |
| Peak torque                                                 | 0.83 Nm                                                               |
| Nominal rotary speed                                        | 7000 rpm                                                              |
| Max. rotational speed                                       | 15600 rpm                                                             |
| Max. mechanical speed                                       | 15000 rpm                                                             |
| Angular acceleration                                        | $\leq 100000 \text{ rad/s}^2$                                         |
| Nominal power rating of motor                               | 154 W                                                                 |
| Continuous stall current                                    | 1.3 A                                                                 |
| Nominal motor current                                       | 1.2 A                                                                 |
| Peak current                                                | 5.4 A                                                                 |
| Motor constant                                              | 0.175 Nm/A                                                            |
| Standstill torque constant                                  | 0.24 Nm/A                                                             |
| Voltage constant, phase-to-phase                            | 14.6 mV/min                                                           |
| Phase-phase winding resistance                              | 13.1 Ohm                                                              |
| Phase-phase winding inductance                              | 13.9 mH                                                               |
| Winding longitudinal inductivity Ld (phase)                 | 5.3 mH                                                                |
| Winding cross inductivity Lq (phase)                        | 6.9 mH                                                                |
| Electric time constant                                      | 1.06 ms                                                               |
| Thermal time constant                                       | 4.6 min                                                               |
| Thermal resistance                                          | 1.58 K/W                                                              |
| Measuring flange                                            | 200 x 200 x 15 mm, steel                                              |
| Total mass moment of inertia of output                      | 0.039 kgcm <sup>2</sup>                                               |
| Product weight                                              | 500 g                                                                 |
| Permissible axial shaft load                                | 30 N                                                                  |
| Permissible radial shaft load                               | 150 N                                                                 |
| Rotor position sensor                                       | Absolute encoder, multi-turn                                          |
| rotor position sensor, manufacturer designation             | EQI 1131                                                              |
| rotor position sensor, absolute detectable revolutions      | 4096                                                                  |
| Rotor position encoder interface                            | EnDat 22                                                              |
| Rotor position sensor, encoder measuring principle          | Inductive                                                             |
| rotor position sensor, DC operating voltage                 | 5 V                                                                   |
| rotor position sensor, DC operating voltage range           | 3.6 V ... 14 V                                                        |
| rotor position sensor, position values per revolution       | 524288                                                                |
| Rotor position transducer resolution                        | 19 bit                                                                |
| rotor position sensor, system accuracy of angle measurement | -120 arcsec ... 120 arcsec                                            |
| Mean time to failure (MTTF), subcomponent                   | 190 years, rotor position encoder                                     |