



Connectors > Automotive Connectors > Automotive Housings > AMP Unsealed Connector Housing



Number of Positions: 9

Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: 1.6 mm [.063 in]

Connector System: **Wire-to-Wire**

Centerline (Pitch): 4 mm [.157 in]

[All AMP Unsealed Connector Housing \(110\)](#)

Features

Electrical Characteristics

Operating Voltage	36 VDC
-------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Dimensions

Product Width	4.2 mm[.165 in]
Product Length	37.2 mm[1.46 in]
Connector Height	23.5 mm[.925 in]

Packaging Features

Packaging Method	Box
Packaging Quantity	1000

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No



Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Other

Serviceable	Yes
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Body Features

Cable Exit Angle	180°
Primary Product Color	Natural
Connector & Keying Code	B

Housing Features

Housing Material	PBT GF20
Centerline (Pitch)	4 mm[.157 in]

Contact Features

Contact Size	1.5K
Contact Type	Receptacle
Mating Tab Width	1.6 mm[.063 in]

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
Number of Rows	1

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
-----------------------------	----------------



Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2364901-2
36POS. AMP MCP 1,5K, REC HSG ASSY, UNSLD



TE Part # CAT-AM705-CH8173
AMP Unsealed Connector Housing



TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB



TE Part # 1-1579007-1
EXTRACTION TOOL



TE Part # 1-1670615-1
36POS, MIXED, HEADER ASSY, CONV. KIT 25POS

TE Part # 1-2112891-6
36POS, TAB 1.5X0.6, TAB HSG, ASSY

TE Part # 1-2141847-4
CARRIER, RECEPTACLE HSG, 36POS, ASSY

TE Part # CAT-M4599-B128
AMP Carrier for Receptacle Inserts

TE Part # 2-1670615-1
36POS, MIXED, HEADER ASSY, CONV. KIT 25POS

TE Part # 1-1718492-4
1.5MM TAB HSG 36 POS ASSY

TE Part # 1-2112891-5
36POS, TAB 1.5X0.6, TAB HSG, ASSY

TE Part # 1-1718492-5
1.5MM TAB HSG 36 POS ASSY

TE Part # 1-1718492-3
1.5MM TAB HSG 36 POS ASSY

Also in the Series | AMP MCP 1.5K

Automotive Connector Caps & Covers (24)

Automotive Housings (265)


Automotive Terminals (7)

Insertion & Extraction Tools (13)

Also in the Series | AMP MCP Connector System




Automotive Connector Caps & Covers
(24)




Automotive Connector Locks &
Position Assurance(4)



Automotive Headers(31)



Automotive Housings(265)



Automotive Terminals(7)




Connector Seals & Cavity Plugs(5)




Insertion & Extraction Tools(13)



Other Automotive Connector
Accessories(2)



PCB Headers & Receptacles(31)



Wire-to-Board Headers & Receptacles
(30)

Customers Also Bought



TE Part #1534594-3
MCON 1.2 CB REC SRC AG




TE Part #5677672002
RNF-3000-24/8-2-STK



TE Part #CAT-AM705-CH8173
AMP Unsealed Connector Housing




TE Part #1-2112035-1
26POS, MIXED,REC HSG,ASSY,
SEALED



TE Part #6-2176607-4
RLC73PD 3A R255 1% 1K RL



TE Part #1-1718485-4
CARRIER FOR RECEPT INSERTS 36
POS



TE Part #1-1718492-3
1.5MM TAB HSG 36 POS ASSY

Documents



Product Drawings

AMP MCP 1.5 RECEPT HSG 9 POS

English

CAD Files

Customer View Model

ENG_CVM_1718490-2_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_1718490-2_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_1718490-2_A1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German