

Series AS5

Qn = 14500 l/min



Technical data

Industry

Industrial

Parts

Reservoir

Reservoir

reservoir, metal, with inspection glass

Filter reservoir volume

87 cm³

Condensate drain

semi-automatic, open without pressure

inspection glass

with window

Max. working pressure

16 bar

Min. ambient temperature

-10 °C

Max. ambient temperature

50 °C

Min. medium temperature

-10 °C

Max. medium temperature

50 °C

Medium

Compressed air

Weight

0.68 kg

Material

Material reservoir

Die cast zinc

Seal material

Acrylonitrile butadiene rubber

Part No.

R412009344


Technical information

The pressure dew point must be at least 15 °C less than ambient and medium temperature and may not exceed 3 °C.

The oil content of compressed air must remain constant during the life cycle.

Use only the approved oils from AVENTICS. Further information can be found in the “Technical information” document (available in <https://www.emerson.com/en-us/support>).

Dimensions



Dimensions in mm

| Part No. | A | B | C |
|------------|----|-------|------|
| R412009338 | 60 | 165.3 | 64.7 |

Reservoir, Series AS5-CLS/ -CLP/ -CLC

2024-03-20

R412009344

| Part No. | A | B | C |
|------------|----|-------|------|
| R412009344 | 60 | 165.3 | 64.7 |