




IO-Link CompactLine module

IO-Link module 4 DI M8 IP 67



Electrical data

Operating voltage	[V]	18...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	50
Sensor supply US		
Current rating per port	[A]	0.1

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4
------------------------------	-----------------------------

Inputs

Number of digital inputs		4
Input circuit of digital inputs		PNP
Input current limitation	[mA]	15
Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes

Interfaces

Communication interface	IO-Link	
Supported DeviceIDs	Type of operation	DeviceID
	default	789



IO-Link CompactLine module

IO-Link module 4 DI M8 IP 67

IO-Link Device		
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
SIO mode	no	
Process data binary	32	
Min. process cycle time	[ms]	2.9
Operating conditions		
Ambient temperature	[°C]	-25...70
Storage temperature	[°C]	-25...85
Max. relative air humidity	[%]	90; (non condensing)
Protection	IP 67	
Protection rating (NEMA 250)	6P	
Chemical media	ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA
	NEMA 250 5.13.1	AA
Tests / approvals		
EMC	EN 61000-6-2	
	EN 61000-6-3	
	IEC 61131-9	
Mechanical data		
Weight	[g]	105.5
Housing	rectangular	
Type of mounting	backplane mounting	
Dimensions	[mm]	85.5 x 30 x 23.7
Materials	PBT; socket: brass nickel-plated; O-ring: FKM	
Sealing material	FKM	
Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow
Accessories		
Items supplied	panel for labelling	
	Protective caps: 2	
Accessories (optional)	Protective cap: M8, E73005	
Remarks		
Remarks	For use in NFPA 79 applications only	
	The device is to be operated to IO-Link specification V1.1.2.	
	The maximum cable length of the IO-Link cable is 20 m.	
Pack quantity	1 pcs.	



IO-Link CompactLine module

IO-Link module 4 DI M8 IP 67

Electrical connection - IO-Link


Connector: 1 x M12; coding: A



	IO-Link
1	L +
2	not used
3	L -
4	C/Q / IO-Link

Electrical connection - Inputs

Connector: 4 x M8; coding: A; Sealing: FKM



	Inputs X1.0...X1.3
1	Sensor supply +24 V
3	Sensor supply -
4	data input