


## Technical data sheet

Article number:  
170-40302

HEGPA6603



<b>Product Group</b>	Abrasion-resistant polyamide braided sleeving
<b>Product Family</b>	Helagaine HEGPA66
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Colour</b>	Grey (GY)
<b>Application Method</b>	Fraying of the braided sleeving can be avoided by using a hot-knife to cut the sleeving. Braided sleeving can also be supplied in pre-cut lengths on request.
<b>Bundle Ø max.</b>	4 mm
<b>Bundle Ø min.</b>	2 mm
<b>Melting Point</b>	+255 °C
<b>Operating Temperature</b>	-60 °C to +150 °C
<b>Pack Cont.</b>	10 m
<b>Package Content packed in</b>	reel

HF ✓ RoHS ✓