

Swivel Stem Castor, grey rubber 100mm, 60kg

Swivel Stem Castor

PRODUCT

Article number

DP3FA100-325L12

DP3FD100-325L12



Product Details

Castor assembly : Pressed steel, zinc plated housing, with threaded stem fitting.

Swivel : Swivel on two rows of balls.

Double-acting lock on wheel and pivot. Grey nylon pedal.

Rim : Grey Polypropylene.

Tread : Grey synthetic Rubber. Non-marking.

Hub : Plain bearing.

Specifications

	Threaded Stem	
Wheel Diameter - ØD ± 1%	100 mm	
Hub Type	Plain bore	
Hub Length	28 mm ±1	
Width of Tread	26 mm ±1	
Width of Tread-on floor	26 mm ±1	
Overall Height	134 mm	
Offset	35 mm	
Fitted Stem Diameter	12 mm	
Fitted stem Height	30 mm	
Hardness of tread A ±3	A 80° Shore	
Load capacity	60 Kg	
Temperature	-5 / +50 °C	
Weight	Swivel = 0,41 kg	Swivel+brake= 0,46 kg

TECHNICAL DATA

Applications :

Medium-weight appliances and furniture.

Non-marking. Materials handling on indoor or warehouse floors.

Quiet.

Easy to assemble with the crimped stem.

Stem is united to the housing.