



ENGLISH

# Datasheet

## EES80 Series

80W External Power Supply




### Features:

- 80W external power supply
- Protections: Short circuit/ Overload/ Over voltage
- Input voltage range: 100 to 240VAC
- Fully enclosed plastic case
- Efficiency: Up to 86%
- ErP step2 compliant (level V)
- Dimensions (LxWxHmm) 145x 60x 33
- 1.2m DC cable with 2.1mm connector
- 2 year warranty
- AC inlet C14 socket
- CEC regulation – efficiency level V



ENGLISH



Part Number	Voltage	Rated Current	Efficiency	Line Regulation	Load Regulation	Ripple and Noise	MTBF
	12	6.67A	86%	1%	±5%	2%	400khrs
	15	5.33A	86%	1%	±5%	2%	400khrs
	18	4.44A	86%	1%	±5%	2%	400khrs
	24	3.33A	86%	1%	±5%	2%	400khrs
	48	1.66A	86%	1%	±5%	2%	400khrs