



NWT21

Data

Ordering data

Product type description	NWT21
Article number (order number)	101162206
EAN (European Article Number)	4250116200177
eCl@ss number, Version 9.0	27-37-12-13

Certifications

Certificates	cULus CCC IPA
--------------	---------------------

General data

Product name	NWT - Selector switch
Standards	EN 60947-5-1 IEC/EN 60947-1
Versions	Toggle
Toggle	short
Sealing type	Membrane Lip gaskets
Material of the operators	ABS
Material of the front ring	ABS, chrome-plated
Colour of the front ring	Silver
Colour of the handle	Grey
Gross weight	35 g

General data - Features

Probing possible	Yes
Fully insulated	Yes
Number of plunger	1
Number of switch positions	2

Mechanical data

Unlocking	without
Touch position	right
Mounting	Mounting flange EFM
Switching angle, right	55 °
Tightening torque of the screw	0.6 Nm

Mechanical data - Dimensions

Height	26 mm
diameters for the actuating heads	44.5 mm
Length of the handle	28 mm
Diameter hole	22.3 mm
Diameter hole, with tolerance indication	22.3 + 0.4 mm
Thickness, of the front panel, minimum	1.5 mm
Thickness of the front panel, maximum	6 mm
Spacing	50 x 50 mm

Ambient conditions

Protection class	IP67 IP69K
Ambient temperature, minimum	+0 °C
Ambient temperature, maximum	+80 °C

Documents

Operating instructions and Declaration of conformity

(1,3 MB, 10.05.2019, Revision B)

BG-test certificate

(286,7 kB, 28.04.2020)

UL Certificate

(413,7 kB, 01.08.2019)

IPA Data

(242,8 kB, 10.05.2019, Revision A)

Brochure

(8,7 MB, 10.05.2019, Revision 03)

Pictures

Product picture (catalogue individual photo)



ID: krwsef01


| 95,5 kB | .jpg | 27.093 x 40.64 mm - 320 x 480 Pixel - 300 dpi

| 57,8 kB | .png | 74.083 x 111.125 mm - 210 x 315 Pixel - 72 dpi

| 765,7 kB | .jpg | 352.778 x 529.167 mm - 1000 x 1500 Pixel - 72 dpi

System components

EFMH/SEK - Mounting flange for position switch



101014388 EFM

- mounting flange with Position switch
- 30 mm x 42 mm x 92 mm
- Thermoplastic enclosure

K.A. Schmersal GmbH & Co. KG, Möddinghofe 3, D-42279 Wuppertal

The details and data referred to have been carefully checked. Images may diverge from original. Further technical data can be found in the manual. Technical amendments and errors possible.

Generated on 23.06.2020 13:07:00