

Product data sheet

179 N XXL-7/340

EAN-No. 4000896215072



340-pieces · 7 Drawers total



Application:

Efficient, mobile organisation of tools

- Tool trolley
- 5 flat and 2 high drawers
- Complete with 340-piece tool assortment in Safety-Insert-System soft foam insert

Work areas

- Much larger storage and work areas in stainless steel
- Fully sealed work surface protects inside of trolley from leaking liquids
- Interfaces integrated in the work area for accessories such as laptop holders and top modules
- Stainless steel work surface
- Extra protection through high-quality plastic end caps

Body / Pull-handle

- Extremely robust design thanks to dual-wall structure
- Complete welded construction of the entire body for tough daily workshop use
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Ergonomically optimised pull handle for better manoeuvrability
- Brushed stainless steel handle

Locking concept

- Ergonomically arranged side lock position for better operability protects keys and lock against damage
- Highly secure closing system with central locking technology for optimum protection of your property
- 2-stage locking
 - Central locking, lockable with cylinder lock and 2 folding keys
 - Mutual drawer locking for minimum tilting risk

Drawer concept

- Self-closing and reciprocal locking of the drawers prevents unwanted opening
- 100% sliding-out with ball-bearing telescopic slides
- Drawer design for optimum use of the interior
- Drawer fronts for optimised handling
- Dirt-resistant drawer coating for easy cleaning

High performance chassis

- Large wheels with high loading capacity, precision ball bearing and dual rounded rim in the pivot bearing, easy manoeuvrability, even with high dynamic load
- 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
- Protective ring prevents dirt and threads from getting in

Product data sheet

179 N XXL-7/340

EAN-No. 4000896215072



850LG • • 1/4
4 • 5 • 6 • 7 • 8 • 9 • 10 •
11 • 12 • 13

8501 • • 1/4
3 • 4 • 5 • 6 • 8

8502 • • 1/4
T15 • T20 • T25 • T27 •
T30 • T40

8503 • • 1/4
0.6 x 3.5 • 1 x 5.5 • 1.2 x 8

8506 • • 1/4
PH1 • PH2

8507 • • 1/4
PZ1 • PZ2



858-1 • 3/8 • 1/4



863HP • 1/4



865 • 1/4



867-2 • 1/4 • 1/4



868 • 1/4 • 1/4



869 • 1/4 • 1/4

880 • • 3/8
10 • 11 • 12 • 13 • 14 • 15 •
16 • 17 • 18 • 19 • 21 • 22

880LG • • 3/8
12 • 13 • 14 • 15 • 16 • 17 •
18 • 19

8801K • • 3/8
5 • 6 • 8 • 10



8816HP • 3/8



8820 • 3/8 • 3/8

8821 • 3/8 • 3/8
8821-3 • 8821-6 • 8821-10

900 • • 1/2
10 • 11 • 12 • 13 • 14 • 15 •
16 • 17 • 18 • 19 • 20 • 21 •
22 • 23 • 24 • 26 • 27 • 28 •
30 • 32



915 • 1/2



916HP • 1/2

917-5 • 1/2 • 1/2

918-10 • 1/2 • 1/2



920 • 1/2 • 1/2

986 • • 1/2
4 • 5 • 6 • 7 • 8 • 9 • 10 •
12 • 17 • 19 • 22

990 • • 1/2
M5 • M6 • M8 • M10 • M12 •
M14 • M16 • M18

991 • • 1/2
M6 • M7 • M8 • M9 • M10 •
M12 • M14

992 • • 1/2
T20 • T25 • T27 • T30 •
T40 • T45 • T50 • T55 • T60

2204N • • 1/4
2 • 2.5 • 3 • 4 • 5 • 6

2208N • • 1/4
0.5 x 4 • 0.6 x 4.5 •
0.8 x 5.5 • 1 x 6

2215N • • 1/4
PH1 • PH2 • PH3

2216N • • 1/4
PZ1 • PZ2 • PZ3

2223N • • 1/4
T6 • T7 • T8 • T9 • T10 •
T15 • T20 • T25 • T27 •
T30 • T40

2223N • • 1/4
T10H • T15H • T20H •
T25H • T27H • T30H



2239N-6 • 1/4 • 1/4

2250-1 • 1/4 • 1/4



163-509/12 •

606 •
8 • 9 • 10 • 11 • 12 • 13 •
14 • 15 • 16 • 17 • 18 • 19



163-510/8

730
730-3 • 730-6



751HS/5



163-511/4



760-2

1802M-22



1841MB-33

1850M-22



2128N-1