
## MBR(F,B)10H90, MBR(F,B)10H100

Vishay General Semiconductor

RoHS

## **High Voltage Schottky Rectifier**

High Barrier Technology for Improved High Temperature Performance



PRIMARY CHARACTERISTICS					
I <sub>F(AV)</sub>	10 A				
$V_{RRM}$	90 V, 100 V				
I <sub>FSM</sub>	250 A				
$V_{F}$	0.64 V				
I <sub>R</sub>	4.5 μA				
T <sub>J</sub> max.	175 °C				

### **FEATURES**

- Guardring for overvoltage protection
- · Low power loss, high efficiency
- · Low forward voltage drop
- · Low leakage current
- High forward surge capability
- High frequency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 245 °C (for TO-263AB package)
- Solder bath temperature 275 °C maximum, 10 s, per JESD 22-B106 (for TO-220AC and ITO-220AC package)
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see <a href="https://www.vishay.com/doc?99912">www.vishay.com/doc?99912</a>

#### TYPICAL APPLICATIONS

For use in high frequency rectifier of switching mode power supplies, freewheeling diodes, DC/DC converters or polarity protection application.

### **MECHANICAL DATA**

Case: TO-220AC, ITO-220AC, TO-263AB

Molding compound meets UL 94-V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/NHE3 - RoHS-compliant, AEC-Q101 qualified

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix

meets JESD 201 class 2 whisker test

Polarity: As marked

Mounting Torque: 10 in-lbs maximum

MAXIMUM RATINGS (T <sub>C</sub> = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	MBR10H90	MBR10H100	UNIT		
Maximum repetitive peak reverse voltage	$V_{RRM}$	90 100		V		
Working peak reverse voltage	$V_{RWM}$	90 100				
Maximum DC blocking voltage	$V_{DC}$	90	100			
Maximum average forward rectified current	I <sub>F(AV)</sub>	10		A		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	250				
Peak repetitive reverse current at t <sub>p</sub> = 2.0 μs, 1 kHz	I <sub>RRM</sub>	0.5				
Voltage rate of change (rated V <sub>R</sub> )	dV/dt	10 000		V/µs		
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	- 65 to 175		°C		
Isolation voltage (ITO-220AC only) from terminal to heatsink t = 1 min	$V_{AC}$	1500		V		



# MBR(F,B)10H90, MBR(F,B)10H100

# Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>C</sub> = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS		VALUE	UNIT	
Maximum instantaneous forward voltage	V <sub>F</sub> <sup>(1)</sup>	I <sub>F</sub> = 10 A	T <sub>C</sub> = 25 °C	0.77	V	
		I <sub>F</sub> = 10 A	T <sub>C</sub> = 125 °C	0.64		
		I <sub>F</sub> = 20 A	T <sub>C</sub> = 25 °C	0.88		
		I <sub>F</sub> = 20 A	T <sub>C</sub> = 125 °C	0.73		
Maximum reverse current	I <sub>R</sub> <sup>(2)</sup>	Rated V <sub>R</sub>	T <sub>J</sub> = 25 °C	4.5	μA	
			T <sub>J</sub> = 125 °C	6.0	mA	

#### Notes

 $^{(1)}\,$  Pulse test: 300  $\mu s$  pulse width, 1 % duty cycle

(2) Pulse test: Pulse width  $\leq$  40 ms

THERMAL CHARACTERISTICS (T <sub>C</sub> = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	MBR	MBRF	MBRB	UNIT
Typical thermal resistance	$R_{ heta JC}$	2.7	5.8	2.7	°C/W

ORDERING INFORMATION (Example)							
PACKAGE	PREFERRED P/N	UNIT WEIGHT (g)	PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
TO-220AC	MBR10H100-E3/45	1.80	45	50/tube	Tube		
ITO-220AC	MBRF10H100-E3/45	1.94	45	50/tube	Tube		
TO-263AB	MBRB10H100-E3/45	1.33	45	50/tube	Tube		
TO-263AB	MBRB10H100-E3/81	1.33	81	800/reel	Tape and reel		
TO-220AC	MBR10H100HE3/45 (1)	1.80	45	50/tube	Tube		
ITO-220AC	MBRF10H100HE3/45 (1)	1.94	45	50/tube	Tube		
TO-263AB	MBRB10H100HE3/45 (1)	1.33	45	50/tube	Tube		
TO-263AB	MBRB10H100HE3/81 (1)	1.33	81	800/reel	Tape and reel		

### Note

(1) AEC-Q101 qualified

T<sub>.1</sub> = 150 °C

# Vishay General Semiconductor

### **RATINGS AND CHARACTERISTICS CURVES**

(T<sub>A</sub> = 25 °C unless otherwise noted)





Fig. 1 - Forward Current Derating Curve



10 000




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 5 - Typical Junction Capacitance




Fig. 3 - Typical Instantaneous Forward Characteristics





Fig. 6 - Typical Transient Thermal Impedance




## MBR(F,B)10H90, MBR(F,B)10H100


## Vishay General Semiconductor

### PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



#### TO-263AB







### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000