



# 739-8408 Data Sheet

ENGLISH

Model number : 739-8408  
Type of tool : 6" Orbital Sander  
Power Source : Compressed air  
Maximum permissible operating pressure : 90 psi ( 6.2 bar )  
Recommended operating pressure : 90 psi ( 6.2 bar )

## 739-8408

### 6" Orbital Sander

### Technical Data

#### Features

- Two handed operation
- With built in speed regulator
- Rear exhaust
- Insulated handle and motor housing
- Random orbit
- Positive lever action
- Includes 150mm diameter backing pad for self-adhesive abrasives

#### Specifications

- Material: Aluminium
- Size: 8mm Random Orbit
- Free Speed: 10,000RPM
- Pad Size: 150mm / 6"
- Weight: 2.7kgs / 6lbs
- Length: 10.2" / 260mm
- Min Hose Size: 3/8" / 10mm
- Air inlet thread: 1/4"
- Sound: 96dBA
- Vibration: 4.4m/s<sup>2</sup>
- Ave Air Consumption: 3.5cfm / 100 l/min
- Recommended lubrication: 10 Weight SAE Oil



#### Declaration of Conformity

We	RS Components Ltd
declare under our sole responsibility that the	739-8408 – 6" Orbital Sander
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927