

XVC6M4

Complete pre wired monolithic tower light,
Harmony XVC, plastic, red orange green
blue, 60mm, tube mounting, steady, IP23,
100...240V AC

Main

Range of product	Harmony XVC6
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	4 illuminated units
Sound signalling	Without
Mounting diameter	60 mm
Component name	XVC
Light source	LED steady red LED steady orange LED steady green LED steady blue
[Us] rated supply voltage	100...240 V
Supply circuit type	AC

Complementary



Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94-V0): top cover
Product mounting	On support tube, 22 mm
Cable cross section	0.33 Mm ² 0.83 mm ²
AWG gauge	AWG 18 AWG 22
Cable length	550 Mm 450 mm
Marking	CE
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	75 mA
Net weight	1.12 kg
Height	719.8 mm

Environment

Standards	IEC 60947-1 IEC 60947-5-1
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Electrical shock protection class	Class I conforming to IEC 61140
IP degree of protection	IP23 vertical surface installation conforming to IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins