




---

 PRODUCT-DETAILS

# OTR75A3B

## OTR75A3B Safety switch




---

### General Information

Extended Product Type	OTR75A3B
Product ID	1SCA022567R8960
EAN	6417019183114
Catalog Description	OTR75A3B Safety switch
Long Description	<p>Safety switch, 3-p. 415V AC23 80A, 37kW. Mounted auxiliary contact: 1NO0NC. Stainless steel enclosure. IP65. RedYellow Pistol handle. Interlocked cover. Defeatable interlocking.</p> <p>The enclosure of the OTR series is made of rigid stainless steel, class AISI304. The enclosure has a hinged door, with door lock. The cover is interlocked, and can not be opened when switch is on. The interlock function can be defeated for thermographing. Suitable for outdoor and indoor use. The cable entries are of knock out types. PE terminal and auxiliary contact included. Can be used in EMC application, if EMC cable glands are used.</p>

---

### Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control	1SCC340095D0201

Act - TSCA

---

## Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340006M0013
Mechanical Drawings	OTLK302013PBB.stp

---

## Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

---

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Last Ordering Date	2026-08-31 All Countries
Replacement Product ID (NEW)	OTR80GA3M
Country or Territory of Origin	Bulgaria

---

## Dimensions

Product Net Width	200 mm
Product Net Height	300 mm
Product Net Depth / Length	135 mm
Product Net Weight	3.1 kg

---

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	212 mm
Package Level 1 Depth / Length	313 mm
Package Level 1 Height	191 mm
Package Level 1 Gross Weight	3.3 kg
Package Level 1 EAN	6417019183114

---

## Technical

Cable Cross-Section	10 ... 70 mm <sup>2</sup>
Cable Entry Position	Top and/or Bottom
Cable Outlets Per Side	B-flange / B-flange
Color	Stainless
Connecting Capacity Main Circuit	Screw Clamp 10 ... 70 mm <sup>2</sup> Screw Clamp / PE Terminal 2pc, 10 ... 70 mm <sup>2</sup>
Conventional Thermal Current (I <sub>the</sub> )	Fully Enclosed 115 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Stainless steel
Handle Color	Red / Yellow

Handle Type	Pistol handle
Impact Resistance Rating	Housing IK09
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC
Mounted Auxiliary Contacts	1 NO, 0 NC
Neutral Type	No Neutral Terminal
Number of Auxiliary Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Poles	3P
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out
Position of PE Terminals	Top In - Bottom Out
Power Loss	at Rated Operating Conditions per Pole 4 W
Rated Insulation Voltage (U <sub>i</sub> )	acc. to IEC/EN 60664-1 750 V
Rated Operational Current AC-22A (I <sub>e</sub> )	(380 ... 415 V) 100 A (500 V) 100 A (690 V) 100 A
Rated Operational Current AC-23A (I <sub>e</sub> )	(380 ... 415 V) 80 A (500 V) 60 A (690 V) 40 A
Rated Operational Power AC-23A (P <sub>e</sub> )	(380 ... 415 V) 37 kW (500 V) 37 kW (690 V) 37 kW
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity (I <sub>cm</sub> )	(690 V AC) 3.6 kA
Rated Short-time Withstand Current Low Voltage (I <sub>cw</sub> )	for 1 s 2.5 kA
Recommended Screw Driver	Main Circuit Hexagon 4
Special Functions	EMC
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 6 N·m
Wire Stripping Length	20 mm

### Technical UL/CSA

Wire Stripping Length	20 mm
Recommended Screw Driver	Main Circuit Hexagon 4
Tightening Torque	Main Circuit 6 N·m

### Certificates and Declarations

Declaration of Conformity - CE	1SCC340006D2704
--------------------------------	-----------------

### External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch

---

## Categories

---

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

