



All AMPOWER Terminal, 1 Stud Hole, Large (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 55830-2
[TERM,AMPWR 646MCM \(2\)3/8](#)




TE Part # 46757-2
[HYP8 AMPPOWER 700MCM DIE SET](#)


Customers Also Bought



TE Part #CAT-P592-R472
[PIDG Radiation Resistant C Rings /Spades](#)



TE Part #330368
[SPLICE,SOLIS BUTT 16-14](#)



TE Part #330367
[SPLICE,SOLIS BUTT 22-16](#)



TE Part #324457
[SPLICE,AMPOWER BUTT 2](#)



TE Part #8-36154-5
[PIDG R 22-16 COMM 22-18 MIL 10](#)



TE Part #1-1393139-1
[MDR-137-8=MDR](#)

Documents

Product Drawings

[TERMINAL,AMPOWER 700MCM 1/2](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_326305_R.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_326305_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_326305_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

AMPOWER Terminals and Splices Flyer

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English