

# 17" LED Monitor with BNC port

Art. no. TVAC10012

Page 1 of 3



- Resolution: 1280 x 1024 pixels
- Fast reaction time (5 ms)
- LED background lighting: brilliant colour display and contrast
- Graphical on-screen display (OSD)
- Connections: HDMI, VGA, S-Video, 2x BNC in/out, 2x cinch (audio), PC audio input
- Integrated loudspeaker
- Low power consumption (LED technology)
- For wall and ceiling installation (with VESA mount)

The 17" LED monitor offers outstanding picture quality and rapid reaction times for optimum picture fidelity. With integrated BNC connections and other interfaces, the monitor is well-equipped for the requirements of professional video surveillance. The signal is detected automatically and all settings can easily be configured in the on-screen display (OSD) in several languages. Thanks to energy-saving LED technology, the monitor has a low power consumption, and therefore can be used efficiently for 24/7 operation.

## Detailed surveillance pictures

With its high resolution, outstanding picture fidelity and rapid reaction time, the monitor produces accurate surveillance pictures. The LED backlighting ensures optimum contrast and an extremely realistic colour display. With the picture-in-picture and picture-over-picture functions, multi-tasking is quick and simple. With the aid of picture-in-picture, a small preview window can be conveniently displayed.

## Versatile connections

The HDMI, VGA and BNC video inputs offer flexibility for connecting the monitor to a recorder, live cameras or a computer. Integrated loudspeakers and audio inputs also allow sound signals to be played back. All of these features make the monitor a cost-effective component for versatile surveillance and IT systems.

## Efficient uninterrupted 24/7 use

Thanks to high-quality industry components, the monitor is optimally suited for uninterrupted 24/7 use. The

# 17" LED Monitor with BNC port

Art. no. TVAC10012

Page 2 of 3

---

energy-efficient LED display ensures very low power consumption.

Easy installation

VESA standard mounts allow mounting to a wall or ceiling. This makes installation fast and easy.

# 17" LED Monitor with BNC port

Art. no. TVAC10012

Page 3 of 3

## Technical Data:

Dimensions	372 x 370 x 50 mm
Connections	1 x HDMI, 1 x VGA, 2 x BNC, 1 x PC Audio, 2 x Chinch Audio, 2 x BNC Out
Output	2 x BNC
Horizontal/vertical viewing angle	170° x 160° °
Picture format	4:3
Screen diagonal	17 "
Width	372 mm
Gross weight	4.6 kg
Display surface	matte
EAN	4043158063622
Input	1 x HDMI, 1 x VGA, 2 x BNC, 1 x PC-Audio, 2 x Chinch-Audio
Color levels	16.7 MIO
Frequency range	30-60KHz(H) / 56-75Hz(V) GHz
Housing material	Plastic
Brightness	250 cd/m²
Height	370 mm
Comb filter	3D
Contrast ratio	1.000:1

Length	50 mm
Loudspeaker	2 x 2,5 W
Power consumption	max. 18 W W
Max. operating temperature	45 °C
Max. humidity	70 %
Min. operating temperature	0 °C
Monitor type	LED
Net weight	3.3 kg
Pixel pitch	0.264 x 0.264 (H) x (V) mm
Reaction time	5 ms
Signal detection	Automatic
DC voltage supply	12 V
Power consumption	2 mA
Video system	PAL / NTSC
Certifications	CE