

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX - 2832658

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ethernet Lean Managed Switch with four 10/100 Mbps RJ45 ports and two 10/100 Mbps FX-SC multi-mode ports

Product Description

The compact Lean Managed Switches (LM) enable the flexible and cost-effective creation of managed Ethernet networks in automation applications. Thanks to the wide range of connection versions and the extended temperature range of -40°C to +70°C, it optimally meets the requirements of industrial applications. It supports PROFINET conformance class A. And its integrated software enables the redundant creation, diagnostics, and monitoring of networks using IT standard protocols.


Your advantages

- Web-based management, SNMP
- Compact housing
- Comprehensive fiber optic versions
- Configuration can be stored externally
- 40°C ... +70°C ambient temperature
- Configurable alarm contact



Ethernet EtherNet/IP

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 101127
GTIN	4046356101127
Weight per Piece (excluding packing)	230.000 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX - 2832658

Technical data

Dimensions

Width	45 mm
Height	99 mm
Depth	112 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Air pressure (operation)	80 kPa ... 108 kPa (2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 108 kPa (3000 m above sea level)

Interfaces

Interface	Ethernet (RJ45)
No. of ports	4 (RJ45 ports)
Note on the connection method	Auto negotiation and autocrossing
Transmission physics	Copper
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Interface	Ethernet FO
No. of ports	2 (SC multi-mode)
Transmission physics	multi-mode fiberglass
Transmission speed	100 Mbps (full duplex)
Transmission length	8000 m (fiberglass with F-G 62.5/125 0.7 dB/km F1000)
	6400 m (fiberglass with F-G 50/125 0.7 dB/km F1200)
	3000 m (fiberglass with F-G 62.5/125 2.6 dB/km F600)
	2800 m (fiberglass with F-G 50/125 1.6 dB/km F800)
Wavelength	1300 nm
Interface	Serial (RS-232)
Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)

Function

Basic functions	Store-and-forward switch complies with IEEE 802.3, 2 priority classes according to IEEE 802.1p, TCP/IP protocol, BootP-compatible, port mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), DHCP server, PTCP filter
Management	Web-based management (HTTP)
	SNMP v1/v2
	Serial interface (V.24)
Diagnostic functions	1:1-Portmirroring
Filter functions	Quality of Service
	VLAN (up to 8 VLANs)

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX - 2832658

Technical data

Function

	IGMP Query
	Auto-Query-Port
	Extended Multicast Filtering
Redundancy	STP (Spanning Tree Protocol)
	RSTP (Rapid Spanning Tree Protocol)
	FRD (Fast Ring Detection)
	Large Tree Support
Supported browsers	Internet Explorer 5.5 or higher
PROFINET conformance class	Conformance-Class A
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link/Activity and Speed)
Signal contact control voltage	24 V (typical)
Signal contact control current	100 mA

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V _{pp} (within the permitted voltage range)
Supply voltage range	18.5 V DC ... 30.5 V DC
Typical current consumption	250 mA (at U _S = 24 V DC)

General

Mounting type	DIN rail
Type AX	Block design
Net weight	230 g

Connection data

Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	7 mm

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	Operation/Storage/Transport: 5g, 150 Hz, Criterion 3
Noise emission	EN 61000-6-3/-4

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX - 2832658

Technical data

Standards and Regulations

Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19170401
eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	27250501
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106
eCl@ss 9.0	19170106

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734
ETIM 6.0	EC000734
ETIM 7.0	EC000734

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43222612

Approvals

Approvals

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX - 2832658

Approvals

Approvals

PRS / BV / GL / LR / GL-SW / BSH / UL Listed / cUL Listed / EAC / EAC / GL / cULus Listed

Ex Approvals

Approval details

PRS		http://www.prs.pl/	TE/2105/880590/16
BV		http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials	23316/B0 BV
GL		https://approvalfinder.dnvgl.com/	59820-08 HH
LR		http://www.lr.org/en	14/20060
GL-SW			59820-08 HH
BSH		http://www.bsh.de/de/index.jsp	Nr. 584
UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
EAC			EAC-Zulassung

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX - 2832658

Approvals

EAC		RU *- DE.A*30.B.01735
-----	--	--------------------------

GL	
----	--

cULus Listed	
--------------	--

Accessories

Accessories

Drivers and interfaces

Software - FL SNMP OPC SERVER V3 - 2701139



SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems

Software - FL SNMP OPC AGENT V3 - 2701136



SNMP-OPC agent, German and English, for integrating OPC-based automation solutions in company-wide network management systems

End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

Mounting rail adapter

Industrial Ethernet Switch - FL SWITCH LM 4TX/2FX - 2832658

Accessories

DIN rail adapter - FL DIN RA - 2891053



The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.

Patch cable

Patch cable - FL CAT5 PATCH 1,0 - 2832276

Patch cable, CAT5, assembled, 1 m

Programming cable

Connecting cable - COM CAB MINI DIN - 2400127



Connecting cable, for connecting the controller to a PC (RS-232) for PC WORX with flow control, 3 m in length

Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Software - IPASSIGN - 2701094



IPAssign is an easy to use tool for setting the IP address of devices which rely on BOOTP. No installation or administrative rights are required to use IPAssign.

This product is free and only available from the "Downloads" tab.