

SURGE SUPPRESSOR, VARISTOR, AC 48...127V, DC 70...150V, FOR MOTOR CONTACTORS SZ S0,



General technical data:

product brand name		SIRIUS
Product designation		surge suppressor
Size of contactor		S0
Design of the surge suppressor		with varistor
Ambient temperature		
• during storage	°C	-40 ... +80
• during operation	°C	-25 ... +60

Control circuit/ Control:

Type of voltage of the control supply voltage		AC/DC
Control supply voltage frequency		
• 1 rated value	Hz	50
• 2 rated value	Hz	60
Control supply voltage 1		
• at DC		
— Initial rated value	V	70
— Final rated value	V	150
• at AC		






— at 50 Hz Initial rated value	V	48
— at 50 Hz Final rated value	V	127
— at 60 Hz Final rated value	V	127
— at 60 Hz Initial rated value	V	48

Installation/ mounting/ dimensions:


Mounting position		any
Mounting type		clip-on
Width	mm	30
Height	mm	19
Depth	mm	12

Certificates/ approvals:

Certificate of suitability CE / UL / CSA / CCC

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval
			
	UL	EG-Konf.	ABS
		spezielle Prüfbescheinigung n	
			BUREAU VERITAS

Shipping Approval



other

[Bestätigungen](#) [Umweltbestätigung](#)



Railway

[Schwingen/Schocke](#)
n

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator




<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT29261BC00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT29261BC00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT29261BC00&lang=en



last modified:

07.12.2015