

Eaton 001896

Catalog Number: 001896

Eaton xEnergy Safety Ci LV systems LV switchgear. Insulated enclosure open above+below, HxWxD=500x375x225mm



General specifications

| | |
|---|----------------|
| Product Name | Catalog Number |
| Eaton xEnergy Safety Ci empty enclosure insulated | 001896 |
| | EAN |
| | 4015080018964 |
| Product Length/Depth | Product Height |
| 225 mm | 500 mm |
| Product Width | Product Weight |
| 375 mm | 3.828 kg |
| Compliances | Certifications |
| RoHS conform | EN 62208 |
| | EN 61439-2 |

Product specifications

Special features

Housing prepared for distribution board Two sides closed, can be folded out two sides open Sealable cover fasteners Integrated pressure-relief mechanism for short-circuits

Type

Basic enclosure Panel enclosures xEnergy Safety Ci

Features

UV resistance beneath protective shield

Cover with overpressure release

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility.

10.13 Mechanical function

Meets the product standard's requirements.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Lower part: 960 °C / cover: 850 °C

10.2.4 Resistance to ultra-violet (UV) radiation

Not relevant to indoor installations.

10.2.5 Lifting

30 kg per enclosure with support frame and lifting aid met; assembled and secured as per the latest applicable instruction leaflet.

10.2.6 Mechanical impact

IK10

10.2.7 Inscriptions

Resources

Brochures

[eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf](#)

[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

Catalogs

[eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf](#)

Drawings

[eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-017.eps](#)

[eaton-enclosures-mounting-xenergy-safety-ci-lv-systems-dimensions-008.eps](#)

[eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-008.eps](#)

[eaton-enclosures-xenergy-safety-ci-lv-systems-dimensions-009.eps](#)

[eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-016.eps](#)

Installation instructions

[05670392.pdf](#)

mCAD model

[ci45_200.dwg](#)

[ci45_200.stp](#)

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

IP65

10.4 Clearances and creepage distances

Is the panel builder's responsibility.

10.5 Protection against electric shock

Protection class 2, therefore not applicable.

10.6 Incorporation of switching devices and components

Is the panel builder's responsibility.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

$U_i = 1000 \text{ V AC}$

10.9.3 Impulse withstand voltage

8 kV

10.9.4 Testing of enclosures made of insulating material

Meets the product standard's requirements.

Surface finishing

Resistant to corrosion

Creepage resistance

KB100, KC200 (cover, to IEC 60112)

KB160, KC175 (base, to IEC 60112)

Degree of protection

IK10

Other

IP65

Enclosure material

Plastic

Surface protection

Other

Chemical resistance

Not resistant to: alkalis, benzene

Partly resistant to: Acids > 10 %

Resistant against: acids < 10 %, mineral oil, alcohol, gasoline, greases, salt solutions

Circuit integrity

Other

Unit type

Single unit

Built-in depth

200 mm

Heat diss. ambient 35°C delta T:20°C wall mount individ. encl.
top (IEC 60890)

36 W

Heat diss. ambient 35°C delta T: 20°C wall mount middle encl.
top (IEC 60890)

31 W

Heat diss. ambient 35°C delta T:20°C wall mount starting encl.
top (IEC 60890)

33 W

Heat diss. ambient 35°C delta T:35°C wall mount individ. encl.
top (IEC 60890)

72 W

Heat diss. ambient 35°C delta T: 35°C wall mount middle encl.
top (IEC 60890)

62 W

Heat diss. ambient 35°C delta T:35°C wall mount starting encl.
top (IEC 60890)

67 W

Color

Gray

Cover/door color

Transparent

Cover/door model

Closed

Cover/door type

Optional

Transparent

None

Number of openings (flange plates)

6

Plate thickness (cabinet)

6 mm

Plate thickness (cover/door)

6 mm

RAL-number

7035

Surface resistance (IEC 60093)

10 TΩ

Width in number of modular spacings

17

Ambient operating temperature details

-40 °C - 80 °C

Material

Glass-fibre reinforced polycarbonate (base)

Non-reinforced polycarbonate (cover)

Halogen free

Mounting method

Surface mounted (plaster)

Number of rows

0

Functions

Extension possible

Temperature resistance

Temperature resistant: 80 °C (gasket)

Temperature resistant: 85 °C (enclosure bolt)

Temperature resistant: -40 °C - 120 °C (enclosure)

Flammability characteristics (UL)

V1 (base) (UL94)

V2 (cover) (UL94)

Protection class

II

Number of modules

1

Surface treatment

Resistant to corrosion

Internal depth

200 mm

Mounting depth with mounting plate

200 mm

Nominal current

1600 A

Number of conduit inlets

104

Suitable for

Outdoor use

Lightning protection

Saline spray resistance

IEC 60068-2-11



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia