

FEATURES

- Heavy duty steel construction
- Adjustable spill retaining shelf
- Non removable sump
- Warning labels

RS PRO Yellow Lockable 1 Doors Hazardous Substance Cabinet, 900mm x 460mm x 460mm

RS Stock No.: 733-4906



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Our RS PRO hazardous substance cabinet is designed to provide safe storage for potentially dangerous substances and materials. Featuring steel construction, 2 Keys are provided with a chrome plated die-cast zinc handle (non snag) and a 2 point steel locking mechanism. A non-removable spillage sump is an integral part of the base to contain spillage. 1 adjustable shelf tray is provided which can retain minor spills and has a galvanised finish.

General Specifications

Number of Doors	1
Number of Shelves	1
Lockable	Yes
Material	Steel
Colour	Yellow
Finish	Powder-Coated
Applications	Schools, Hospitals, Science laboratories, Factories and Offices, Cleaning cupboards

Mechanical Specifications

External Size	900mm x 460mm x 460mm
Height	900mm
Width	460mm
Depth	460mm
Locking Mechanism	2 point steel locking mechanism

Approvals

Compliance/Certifications	COSHH regulations for storage and transportation of hazardous substances
----------------------------------	--



CABINET
SUPPLIED WITH
WARNING
LABELS



Cabinet Size HxWxD(mm)	No. of Shelves Supplied	RS Stock No.
900x460x460	1	7334906
700x900x460	1	7334909
900x900x460	1	7334903
1800x900x460	3	7334912