



Product Compliance

For compliance documentation, visit the product page on TE.com>






EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # CAT-076-BNCJKRA75C BNC RF Connector: Jack, Right-angle, 75 Ohm	 TE Part # CAT-076-BNCJKRA754 BNC RF Connector: jack, right-angle, 75 Ohm, 4 GHz	 TE Part # 5-1634503-3 BNC Str PCB Skt 75Ohm Nickel Pltd	 TE Part # 5-1634514-1 BNC Str Jk Hex 75Ohm Nickel Pltd RG59B/U
 TE Part # 1-1634624-0 BNC Ins LP PCB Skt 75Ohm Black	 TE Part # 5222132-1 JACK,VERTICAL,PCB,75 OHM,BNC	 TE Part # 5-1634504-2 BNC Ins BHSkt 75Ohm Nickel Gold Pltd	 TE Part # 1-1634622-0 BNC Ins R/A PCB Skt 75Ohm Black
 TE Part # 1-1634629-0 BNC Ins Str PCB Skt 75Ohm Black	 TE Part # 5-1634516-5 BNC RM BHJ Hex 75Ohm Nickel Pltd RG59B/U	 TE Part # 5221221-5 JACK BLKHD 75OHM BNC	 TE Part # 5414217-1 BNC SOLDER RCPT
 TE Part # 6274359-1 JACK, VERT,PCB,75 OHM,BNC	 TE Part # CAT-076-BNCVTBAY BNC Vertical Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism	 TE Part # CAT-076-BNCJKRA75E BNC RF Connector: 75 Ohm	 TE Part # 5414094-2 JACK,DECOUPLER,R/A,75 OHM, BNC
 TE Part # 414217-1 BNC SOLDER RCPT	 TE Part # 58425-1 DIE,COAX 213/255X042 SQ IS9657	 TE Part # 58531-1 AMP PRO-CRIMPER ASSEMBLY	 TE Part # 1274291-1 JACK,PCB,COML BNC, 75OHM

Customers Also Bought



TE Part #1487594-2
USB, A-B, 28/28, BLACK, 0.25M




TE Part #1658621-1
10 NOVO MIL/CTR 15DP,LEAD FREE



TE Part #1-1625886-8
1W SM M/OX 5% 470R



TE Part #5053092090
RNF-100-1/4-0-STK



TE Part #1-215911-4
14 WAY GREY MK II RECP



TE Part #3-1617033-2
HFW1230K07M = M39016/6-205M



TE Part #ZPF000000000003717
732-8052-10 A

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_413589-9_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_413589-9_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_413589-9_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

PRODUCT SPECIFICATION, CONNECTOR, COAXIAL, 50 AND 75 OHM COMMERCIAL BNC DUAL CRIMP TYPE

English

Product Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English



Instruction Sheets
Instruction Sheet (U.S.)
English