


PCB TERMINAL BLOCKS

3.5mm Pitch Pluggable Rising Clamp Terminal Blocks

- 2-8 Pole solid block
- Pluggable male-female connectors
- Closed headers
- Polarised mouldings
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 1.0mm² (28-16AWG) solid & stranded cable
- Anti solder wicking
- Captive screws
- Guided pin alignment
-  approved

SPECIFICATION

Rating	UL=8A/300V, VDE=10A/250V
Insulation resistance	500M Ω/500V
Withstand voltage	AC2000V/1min
Contact resistance	20mΩ (max)
Working temperature	-40°C to 105+°C
Mouldings	UL94-V0 flame retardant PA66
Pin/terminal	Tin plated brass
Rising clamp	Brass, nickel plated
Screw/torque	M2 steel, zinc plated 0.2Nm
Recommended PCB hole size	ø1.4mm

Female Connector

TYPE NO.	POLES	LENGTH
1444292 & 1444063	2	7.8mm
1444298 & 1444064	3	11.3mm
1444304 & 1444065	4	14.8mm
1444066 & 1444313	5	18.3mm
1444067 & 1444322	6	21.8mm
1444329	7	25.3mm
1444069 & 1444334	8	28.8mm

