


TA3405



Temperature transmitter

TA-030C5ER12-A-ZVG/US



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1	
Measuring range	-50...150 °C	-58...302 °F
Process connection	threaded connection G 1/2 external thread	
Installation length EL [mm]	30	

Application

Special feature	Gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating [bar]	400	

Electrical data

Operating voltage [V]	10...30 DC	
Current consumption [mA]	< 30	
Protection class	III	
Reverse polarity protection	yes	

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1	
------------------------------	-------------------------------	--

Outputs

Total number of outputs	1	
Output signal	analogue signal	
Number of analogue outputs	1	
Analogue current output [mA]	4...20	
Max. load [Ω]	(U _b - 8,5 V) / 21,5 mA; 24 V: 720 Ω	
Short-circuit protection	yes	
Overload protection	yes	

Measuring/setting range

Probe length L [mm]	16	
Measuring range	-50...150 °C	-58...302 °F

Resolution

Resolution of analogue output [K]	0.04	
-----------------------------------	------	--

TA3405



Temperature transmitter

TA-030C5ER12-A-ZVG/US

Accuracy / deviations

Precision analogue output	[K]	$\pm 0,3 + (\pm 0,1 \% \text{ MS})$
Temperature coefficient	[% of the span / 10 K]	0,1; (in case of deviation from the reference condition $25 \pm 5^\circ \text{C}$)

Response times

Dynamic response T05 / T09	[s]	1 / 3; (to DIN EN 60751)
----------------------------	-----	--------------------------

Operating conditions

Ambient temperature	[°C]	-40...100
Storage temperature	[°C]	-40...100
Protection		IP 68; IP 69K

Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
UL approval	power supply	Class 2
	UL Approval no.	K005
	File number UL	E217884

Mechanical data

Weight	[g]	122.7
Housing		cylindrical
Dimensions	[mm]	$\varnothing 18.8 / L = 85.3$
Materials		stainless steel (316L/1.4404); PEI; FKM
Materials (wetted parts)		stainless steel (316L/1.4404); FKM
Process connection		threaded connection G 1/2 external thread
Probe diameter	[mm]	6
Installation length EL	[mm]	30

Remarks

Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated




TA3405



Temperature transmitter

TA-030C5ER12-A-ZVG/US

Connection



OUT: analogue output
 colours to DIN EN 60947-5-2