



EN ISO 20345:2011



POLAR

ELDORADO ARCTIC GRIP®

89117-15L

S3 HRO HI WR CI SRC
Size: 38-48
Weight: 810 gr.

Fit: 11

Working Environment:

 Cold places, Wood-metal
 carpentry, Mountains, Building


FEATURES

UPPER

 Full Grain-Anilina Leather-Hydro
 1,8-2,0 mm
 Reflex insert

LINING

 3D Air circulation 320 gr.
 GenuineWool Polar

ANTISLIP LINING DUALMICRO

INSOLE

Dual insulation

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE

PU-RUBBER VIBRAM- ARCTIC GRIP

 New polymer blend with an
 advanced filler system. Engineered
 for low temperature use. Improved
 grip on ice or snow. VIBRAM
 performance, quality and
 durability. Self-cleaning outsole,
 designed to all types of ground
 better. With scaff cap.

TECHNOLOGIES

Removable Insole


 Insole perfect for winter use and for
 footwear with protection against cold
 "CI". It consists of a highly resistant
 and absorbing felt piece that keeps
 the foot dry and warm and of an
 aluminised film to isolate the foot
 from the ground.


Protection elements


 RESISTANT
 TO 3.0 mm.
 NAILS

fibercap sxt

 Composite toecap with fiberglass.
 Resistant to over 200J. Non metal
 perforation resistant insert to over
 1100 N with a 3.0 mm truncated cone
 nail. Protection over the entire sole of
 the foot. Flexible and comfortable


Lateral stability

dynamicHC control
 technology

 Ergonomic rigid internal structure. It
 houses the heel into the right seat,
 adjusting the foot support and control
 of the ankle sideways movements. It
 keeps the foot tight to the shoe,
 allowing the perfect fit.


Torsional stability


STABIL ACTIVE

 Support made of rigid plastic
 material. It stabilizes the heel bone,
 the instep and tarsal joints, without
 altering energy absorption. A support
 for the natural movement of the foot;
 it provides comfort and greater
 stability.


Electrical features



Wire Electricity Discharge

 Strip with 4 filaments of carbon fiber,
 ensuring proven anti-static properties
 of the footwear over time.


Other


H-Dry

+WATERPROOF UPPER

 The HDry membrane is hydrophilic
 with high perspiration capacity. It
 guarantees high performance and
 durability, facilitating the
 maintenance of ideal conditions and
 comfort for the user.


SRC (SRA+SRB)


 SOLE 89
 PU - RUBBER
 ARCTIC GRIP

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.62
	HEEL (CONTACT ANGLE °) ≥0.28	0.59
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.22
	HEEL (CONTACT ANGLE °) ≥0.13	0.20

EN ISO 20344:2011